


스토리지 스테이션


AWPR5125-00-A

▶ 제품 규격





▶ 힘 및 모멘트

이 부품으로 인해 적재 스테이션에 가해질 수 있는 최대 힘과 모멘트를 나타냅니다.



Mr [Nm]	600
Mx [Nm]	500
My [Nm]	600
Fa_H [N]	3000
Fa_V [N]	3000

▶ 수평 구조



▶ 부품 권장



센서



NJR04-E2SK
직선 케이블 0.3 m - 소켓 M8 플러그 연결



	▶ 기술 데이터
주문번호	AWPR5125-00-A
적합	WPR5125L-00-A
인증	LABS / REACH / RoHS
무게 [kg]	0.91

- ⑦ 초기자 마운트
- ⑤① 부착 이동가능한 부품
- ⑦③ 연장 가능한 스트로크
- ⑦⑥ 장착 AWPR
- ⑧① 센서 액추에이터 장착

