


STORAGE STATION


AWPR5200-00-A

PRODUCT SPECIFICATIONS



Forces and moments



Shows the maximum forces and moments which may impact on the storage station due to the loose part



Mr [Nm]	1200
Mx [Nm]	1200
My [Nm]	1200
Fa_H [N]	12000
Fa_V [N]	12000

Horizontal design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Y directions



RECOMMENDED ACCESSORIES



SENSORS



NJR04-E2SK
Inductive Proximity Switch Cable 0,3 m - Connector M8



► Technical Data	
Order no.	AWPR5200-00-A
Compatible with	WPR5200L-00-A
Certifications	LABS / REACH / RoHS
Weight [kg]	2.7

- ⑦ Intake proximity switch
- ⑤① Fastening loose part
- ⑦③ Possible stroke for extending
- ⑦⑥ Fastening AWPR
- ⑧① Fastening sensor actuator

