


# CONNECTING CABLE

## CSTE00368

Order no.	CSTE00368
<b>Technical Data</b>	
Fixing thread	M12
Connection type	Penetration technology
Version	Straight
No. of contacts	5
Coding	A
Rated voltage [V]	125
Current load (at 40°C) [A]	4
Grip body material	TPU
Coupling nut material	Metal, CuZn, nickel-plated
Sealing material	FKM
Cable sheath material	PVC
Cable length [m]	10
Cable-Ø [mm]	5.2
Bending radius for fixed routing, min.	5xØ
Bending radius when using a drag chain, min.	10xØ
Temperature range (fixed) min. [°C]	-30
Temperature range (fixed) max. [°C]	+80
Temperature range (drag chain) min. [°C]	-5
Temperature range (drag chain) max. [°C]	80
Protection to IEC 60529	IP67
Weight [kg]	0.45



- ① BN
- ② WH
- ③ BU
- ④ BK
- ⑤ GY

