


# CONNECTING CABLE

## CSTE00829

Order no.	CSTE00829
<b>Technical Data</b>	
Fixing thread	M12
Connection type	Penetration technology
Connection type	Socket / wire end
Version	Straight
No. of contacts	5
Coding	A
Current load (at 40°C) [A]	4
Coupling nut material	Metal, CuZn, nickel-plated
Cable sheath material	PUR
Cable length [m]	5
Cable-Ø [mm]	5.0
Nr. of wires x diameter [mm <sup>2</sup> ]	5x0.34
Torsion resistant	Yes
Torsion	+/-180°/m, < 2 million cycles
Drag chain-adapted	Yes
Maintenance free (max.)	5 million cycles
Bending radius for fixed routing, min.	5xØ
Bending radius when using a drag chain, min.	10xØ
Temperature range (fixed) min. [°C]	-40
Temperature range (fixed) max. [°C]	+80
Temperature range (drag chain) min. [°C]	-25
Temperature range (drag chain) max. [°C]	80
Protection to IEC 60529	IP67



- ① BN
- ② WH
- ③ BU
- ④ BK
- ⑤ GY

