

CONNECTING CABLE

CSTE01605

Order no.	CSTE01605
Technical Data	
Fixing thread	M12-RJ45
Connection type	Penetration technology
Version	Straight/straight
No. of contacts	4
Coding	D
Current load (at 40°C) [A]	1.5
Rated voltage [V]	60
Grip body material	TPU
Coupling nut material	Metal, CuZn, nickel-plated
Cable sheath material	PUR
Cable length [m]	2
Cable-Ø [mm]	6.7
Nr. of wires x diameter [mm ²]	4x0.34
Flame retardant	Yes
Halogen-free	Yes
Oil resistant	Yes
Drag chain-adapted	Yes
Maintenance free (max.)	3 million cycles
Bending radius for fixed routing, min.	5xØ
Bending radius when using a drag chain, min.	12xØ
Temperature range (fixed) min. [°C]	-40
Temperature range (fixed) max. [°C]	+80
Temperature range (drag chain) min. [°C]	-30
Temperature range (drag chain) max. [°C]	70
Protection to IEC 60529	IP20
Weight [kg]	0.062

