2-JAW PARALLEL GRIPPERS WITH LONG STROKE SERIES GHK6000


PRODUCT ADVANTAGES



"The robust"

- Securing the workpiece in case of drop in pressure above clamping element on the condition of a positive gripper jaw design
- Dimensions based on GH6000 series standard gripper
- Long stroke, up to 200 mm per jaw
- Stable T-slot guide, guided completely along the entire length of the housing
- For gripper fingers with a length of up to 600 mm
- Compact design, through stacked cylinder and guide

THE BEST PRODUCT FOR YOUR APPLICATION






2 Air connection

(4) Air filter

Min./max. operating pressure: 4/7 bar!

TECHNICAL DRAWINGS



TECHNICAL DATA

	Retention force in case of drop in pressure	А	В	с	D	E	F	G
Installation size	[N]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
GHK6140	300	9.6	11.5	21.7	25	17.5	58	22
GHK6160	300	9.6	11.5	21.7	25	37.5	58	22
GHK6180	300	9.6	11.5	21.7	25	57.5	58	22
GHK6240	640	15	14	39.5	35	20	66	27
GHK6260	640	15	14	39.5	35	40	66	27
GHK6280	640	15	14	39.5	35	60	66	27
GHK62100	640	15	14	39.5	35	80	66	27
GHK62150	640	15	14	39.5	35	130	66	27
GHK6360	640	15	14	56	35	47.5	66	27
GHK63100	640	15	14	56	35	87.5	66	27
GHK63150	640	15	14	56	35	137.5	66	27
GHK6460	1050	13.5	20.5	67.4	45	33.5	82	41
GHK64100	1050	13.5	20.5	67.4	45	73.5	82	41
GHK64150	1050	13.5	20.5	67.4	45	123.5	82	41
GHK64200	1050	13.5	20.5	67.4	45	173.5	82	41


FURTHER INFORMATION IS AVAILABLE ONLINE



All information just a click away at: www.zimmer-group.com. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.


2-JAW PARALLEL GRIPPERS WITH LONG STROKE INSTALLATION SIZE GH62100

PRODUCT SPECIFICATIONS



YOU CAN FIND RECOMMENDED ACCESSORIES ON THE FOLLOWING PAGES

	Technical data		
Order no.	GH62100-B	GHK62100	
Stroke per jaw [mm]	100	100	
Gripping force in closing [N]	1350	1350	
Gripping force in opening [N]	1100	1100	
Closing time [s]	0.45	0.45	
Opening time [s]	0.45	0.45	
Dead weight of mounted gripper finger max. [kg]	2.5	2.5	
Length of the gripper fingers max. [mm]	250	250	
Repetition accuracy +/- [mm]	0.05	0.05	
Operating pressure min. [bar]	3	3	
Operating pressure max. [bar]	8	8	
Nominal operating pressure [bar]	6	6	
Operating temperature min. [°C]	+5	+5	
Operating temperature max. [°C]	+80	+80	
Air volume per cycle [cm ³]	458	458	
Protection to IEC 60529	IP40	IP40	
Weight [kg]	5.6	6	



Data, Drawings, 3-D Models, Operating Instructions < www.zimmer-group.com 3