


2-JAW PARALLEL GRIPPERS

INSTALLATION SIZE GP103

▶ PRODUCT SPECIFICATIONS




▶ Gripping force diagram



▶ Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.



Mr	0.5
Mx	0.5
My	0.5
Fa	80

▶ INCLUDED IN DELIVERY



Mounting block

KB4-02



Centering Disc

DST10300

▶ RECOMMENDED ACCESSORIES




Angled Fittings - Barb Style Connection

WVM3




Straight Fittings - Barb Style Connection

GVM3




Inductive proximity switch - Cable 5 m

NJ4-E2



Plug-in connector Angled Cable 5m - Socket M8 (female)

KAW500



Plug-in connector Straight Cable 5m - Socket M8 (female)

KAG500



Universal Jaw Aluminium

UB103



Universal Jaw Steel

UB103ST

Order no.	GP103
Stroke per jaw [mm]	3
Gripping force in closing [N]	21
Gripping force in opening [N]	41
Closing time [s]	0.02
Opening time [s]	0.02
Repetition accuracy +/- [mm]	0.05
Operating pressure min. [bar]	3
Operating pressure max. [bar]	8
Operating temperature min. [°C]	5
Operating temperature max. [°C]	80
Air volume per cycle [cm³]	1
Weight [kg]	0.09

*All data measured at 6 bar

