
2-JAW ANGULAR GRIPPERS **INSTALLATION SIZE GZ25-35G**

▶ PRODUCT SPECIFICATIONS





Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.



Mr	0.5
My	0.8
Fa	50

► RECOMMENDED ACCESSORIES



Straight Fittings - Quick Connect Style

GVM5



Inductive proximity switch - Cable 5 m

NJ3-E2



Inductive Proximity Switch Cable 0,3 m - Connector

NJ3-E2SK



Mounting block

квзм



Plug-in connector Straight Cable 5m - Socket M8 (female)

KAG500



Plug-in connector customizable Straight - Connector M8

S8-G-3



Plug-in connector customizable Straight - Connector M12

S12-G-3

	► Technical Data*
Order no.	GZ25-35G
Stroke per jaw [°]	4
Gripping moment in closing [Nm]	5.4
Gripping moment in opening [Nm]	3.4
Gripping force in closing [N]	135
Gripping force in opening [N]	85
Closing time [s]	0.03
Opening time [s]	0.03
Repetition accuracy +/- [mm]	0.02
Operating pressure min. [bar]	4
Operating pressure max. [bar]	8
Operating temperature min. [°C]	5
Operating temperature max. [°C]	80
Air volume per cycle [cm3]	2
Weight [kg]	0.315

^{*}All data measured at 6 bar

