
2-JAW ANGULAR GRIPPERS INSTALLATION SIZE GZ8-16D

PRODUCT SPECIFICATIONS



RECOMMENDED ACCESSORIES



Straight Fittings - Quick Connect Style

GVM5



Inductive proximity switch - Cable 5 m NJ3-E2



Inductive Proximity Switch Cable 0,3 m - Connector M8 NJ3-E2SK



Mounting block

КВЗМ



Plug-in connector Straight Cable 5m - Socket M8 (female) **KAG500**



Plug-in connector customizable Straight - Connector M8 **S8-G-3**



Plug-in connector customizable Straight - Connector M12 **S12-G-3**

	Technical Data*
Order no.	GZ8-16D
Stroke per jaw [°]	5
Gripping moment in closing [Nm]	0.15
Gripping moment in opening [Nm]	0.15
Gripping force in closing [N]	5.4
Gripping force in opening [N]	5.4
Closing time [s]	0.02
Opening time [s]	0.02
Repetition accuracy +/- [mm]	0.05
Operating pressure min. [bar]	5
Operating pressure max. [bar]	8
Operating temperature min. [°C]	5
Operating temperature max. [°C]	80
Air volume per cycle [cm ³]	0.5
Weight [kg]	0.036

*All data measured at 6 bar

