


# ROUND PLUG

## RSTVLM23G08S-B

Order no.	► Technical Data
Fixing thread	M23
Connection type	Male
Version	Straight
No. of contacts	8
Connecting cross-section	4x0.35 to 2.5 / 4x0.14 to 1.0
Clamping area/outer diameter [mm]	14.0 to 17.0
Connection type	Crimp contacts
Protection to IEC 60529	IP67



PIN assignment

