


ROUND PLUG

RSTVSM23W19S-B

Order no.	Technical Data
Fixing thread	M23
Connection type	Male
Version	Angle
No. of contacts	19
Connecting cross-section	16x0.14 to 1.0 / 3x0.24 to 1.0
Clamping area/outer diameter [mm]	9.5 to 14.5
Connection type	Crimp contacts
Protection to IEC 60529	IP67



PIN assignment

