

ENERGY ELEMENT

WER1500FPL01-03-A

Order no.	► Technical Data
Series	WER1500
Transmission mode	pneumatic
Compatible with installation size	HWR2031 / HWR2040 / HWR2050 / HWR63-B / HWR80-B / WPR5031-A / WPR5040-A / WPR5050-A / WPR5063-A / WPR5080-A / FWR40-B / FWR50-B / FWR63-B / FWR80-B
Compatible with	Fixed part
Number of fluid couplings	1
Fixing thread	G1/4"
Operating pressure [bar]	-0.6 ... 10
Flow per connector [l/min]	500
Connection alignment	radial
Certifications	LABS / REACH / RoHS
Protection to IEC 60529	IP54*
Weight [kg]	0.023

*only in coupled state

