

ENERGY ELEMENT

WER3000FSI08-18-A

Order no.	WER3000FSI08-18-A
Series	WER3000
Transmission mode	electrical
Compatible with installation size	WWR / WWR1000 - 100 / 125 / 160 / 200
Compatible with	Fixed part
No. of contacts	8+2
Connection type	contactless
Nominal current [A]	0.2
Current load per output max. [A]	0.2
Supply voltage [V]	24
Fixing thread	M12
Connection type	Male
Connection type	Round plug
Connection alignment	axial
Protection to IEC 60529	IP67
Weight [kg]	0.24

