





ENERGY ELEMENT


WER3000LEN01-30-A

Order no.	WER3000LEN01-30-A
Series	WER3000
Transmission mode	Communication
Data transmission	Ethernet, Profibus, Profinet, EtherCAT, Interbus, CAN-BUS, USB 2.0, PoE
Compatible with installation size	WPR5100 / WPR5125 / WPR5160 / WPR5200 / WWR1160 / WWR1200
Compatible with	Loose part
Connection category	CAT6a
Data rate [Mbit/s]	10000
Nominal current [A]	0.75
Supply voltage [V]	48
Connection type	RJ45
Connection type	Female connector
Joining force [N]	14
Release force [N]	14
Certifications	LABS / REACH / RoHS
Protection to IEC 60529	IP40*
Weight [kg]	0.1

*only in coupled state



PIN assignment



PIN assignment

