


弹簧推杆

ZLC 系列

产品优点



- ▶ 灵活适用于各种需求
- ▶ 提供内置弹簧与外置弹簧型号
- ▶ 可选配扭转止动器

产品代码

ZLC	M10F	30	TI	3N
系列	固定螺纹	行程 [mm]	真空接口和弹簧位置	规格

技术数据


定购编号	技术数据								
	固定螺纹	行程 [mm]	固定螺纹	螺母数量	螺母扳手尺寸 [mm]	真空接口	真空接口位置	弹簧位置	重量 [kg]
ZLC-12M-30-SE	G1/2" 外螺纹	30	M20X1.5	2	24	G1/8" 内螺纹	侧面	外置	0.289
ZLC-12M-30-TI	G1/2" 外螺纹	30	M22X1.5	2	30	G1/4" 内螺纹	在上	内置	0.13
ZLC-12M-50-SE	G1/2" 外螺纹	50	M20X1.5	2	24	G1/8" 内螺纹	侧面	外置	0.16
ZLC-12M-50-TI	G1/2" 外螺纹	50	M18X1	2	22	G1/8" 内螺纹	在上	内置	0.116
ZLC-12M-50-TI-E	G1/2" 外螺纹	50	M22X1.5	2	30	G1/4" 内螺纹	在上	内置	0.3
ZLC-14M-15-TI	G1/4" 外	15	M18X1	2	22	G1/8" 内螺纹	在上	内置	0.066
ZLC-14M-20-TI	G1/4" 外	20	M16X1	2	20	G1/8" 内螺纹	在上	内置	0.045
ZLC-14M-30-TI-3N	G1/4" 外	30	M18X1	3	22	G1/8" 内螺纹	在上	内置	0.101
ZLC-18F-05-SI	G1/8" 内	5	M10X1	2	12	M5 内部	侧面	内置	0.024
ZLC-18F-10-TI-E	G1/8" 内	10	M16X1	2	20	G1/8" 内螺纹	在上	内置	0.073
ZLC-18M-05-SI	G1/8" 外	5	M10X1	2	12	M5 内部	侧面	内置	0.028
ZLC-18M-10-TI	G1/8" 外	10	M14X1.5	2	19	G1/8" 内螺纹	在上	内置	0.044
ZLC-18M-15-SI	G1/8" 外	15	M14X1	2	19	M5 内部	侧面	内置	0.086
ZLC-18M-15-TI	G1/8" 外	15	M14X1	2	19	G1/8" 内螺纹	在上	内置	0.036
ZLC-18M-18-TI	G1/8" 外	18	M14X1.5	2	20	G1/8" 内螺纹	在上	内置	0.02
ZLC-18M-20-TI-3N	G1/8" 外	20	M18X1	3	22	G1/8" 内螺纹	在上	内置	0.083
ZLC-18M-20-TI-NR	G1/8" 外	20	M16X1	2	20	G1/8" 内螺纹	在上	内置	0.054
ZLC-18M-30-SE	G1/8" 外	30	M14X1.5	2	19	M5 内部	侧面	外置	0.054
ZLC-18M-30-TI	G1/8" 外	30	G1/8"	2	20	G1/8" 内螺纹	在上	内置	0.06
ZLC-18M-30-TI-3N	G1/8" 外	30	M18X1	3	22	G1/8" 内螺纹	在上	内置	0.13
ZLC-18M-45-TE	G1/8" 外	45	M16X1	2	20	G1/8" 内螺纹	在上	外置	0.066
ZLC-18M-50-SE	G1/8" 外	50	M14X1.5	2	19	M5 内部	侧面	外置	0.105
ZLC-18M-50-TE-3N	G1/8" 外	50	M18X1	3	22	G1/8" 内螺纹	在上	外置	0.09
ZLC-18M-50-TI-NR	G1/8" 外	50	M18X1	2	22	G1/8" 内螺纹	在上	内置	0.14
ZLC-18M-70-TE-3N	G1/8" 外	70	M18X1	3	22	G1/8" 内螺纹	在上	外置	0.13
ZLC-M10F-10-TI	M10 内螺纹	10	M16X1	2	14	G1/8" 内螺纹	在上	内置	0.043
ZLC-M10F-20-TI-3N	M10 内螺纹	20	M18X1	3	22	G1/8" 内螺纹	在上	内置	0.083

▶ 技术数据

订购编号	固定螺纹	行程 [mm]	固定螺纹	螺母数量	螺母扳手尺寸 [mm]	真空接口	真空接口位置	弹簧位置	重量 [kg]
ZLC-M10F-30-TI-3N	M10 内螺纹	30	M18X1	3	22	G1/8" 内螺纹	在上	内置	0.122
ZLC-M10F-50-TE-3N	M10 内螺纹	50	M18X1	3	22	G1/8" 内螺纹	在上	外置	0.163
ZLC-M5F-07-TI	M5 内	7	G1/8"	2	14	M5 内部	在上	内置	0.017
ZLC-M5F-07-TI-NR	M5 内	7	G1/8"	2	14	M5 内部	在上	内置	0.018
ZLC-M5F-08-SE	M5 内	8	M10X1	2	14	M5 内部	侧面	外置	0.015
ZLC-M5F-10-TI	M5 内	10	M10X1	2	14	M5 内部	在上	内置	0.036
ZLC-M5F-15-TI	M5 内	15	M10X1	2	14	M5 内部	在上	内置	0.02
ZLC-M5F-20-TI	M5 内	20	G1/8"	2	14	M5 内部	在上	内置	0.02
ZLC-M5M-10-TE	M5 外	10	M12X1	2	14	M5 内部	在上	外置	0.03
ZLC-M5M-20-TE	M5 外	20	M12X1	2	14	M5 内部	在上	外置	0.033
ZLC-NFA-06-TI		6	M8X0.8	2	12	M5 内部	在上	内置	0.012
ZLC-NFA-10-TI		10	M8X1	2	12	M5 内部	在上	内置	0.02
ZLC-NFA-25-TI-NR		25	M8X1	2	12	M5 内部	在上	内置	0.021
ZLC-NFB-05-SI-NR		5	M10X1	1	14	M3 内螺纹	侧面	内置	0.014
ZLC-NFB-06-TI		6	M8X1	2	12	M5 内部	在上	内置	0.011
ZLC-NFB-10-TI		10	M8X1	2	12	M5 内部	在上	内置	0.019
ZLC-NFC-06-TI		6	M8X1	2	12	M5 内部	在上	内置	0.012
ZLC-NFC-10-TI		10	M8X1	2	12	M5 内部	在上	内置	0.02


► 技术图纸

ZLC-12M-30-SE



- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-12M-30-TI




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-12M-50-SE



- ① 固定
③ 真空接口
⑬ 吸唇连接口


ZLC-12M-50-TI



- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口


彈簧推杆 ZLC 系列

ZLC-12M-50-TI-E




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-14M-15-TI




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-14M-20-TI




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-14M-30-TI-3N




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18F-05-SI



- ① 固定 ⑬ 吸唇连接口
③ 真空接口

ZLC-18F-10-TI-E



- ① 固定
③ 真空接口
⑬ 吸唇连接口

-

- [illegible]


Technical drawing of a 1/2 inch NPT x 1/2 inch NPT female-to-male adapter. The side view shows a total length of 1.5 inches, with a 0.5 inch section for the male thread and a 1.0 inch section for the female thread. The top view shows a hexagonal base with a 0.5 inch diameter hole and a 0.75 inch outer diameter.

-

-


彈簧推杆 ZLC 系列

ZLC-18M-20-TI-NR




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18M-30-SE




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18M-30-TI




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18M-30-TI-3N




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18M-45-TE




- ① 固定 ⑬ 吸唇连接口
③ 真空接口

ZLC-18M-50-SE




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18M-50-TE-3N




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18M-50-TI-NR




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-18M-70-TE-3N




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-M10F-10-TI




- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-M10F-20-TI-3N



- ① 固定
③ 真空接口
⑬ 吸唇连接口

ZLC-M10F-30-TI-3N




- ① 固定
③ 真空接口
⑬ 吸唇连接口

弹簧推杆


ZLC 系列

ZLC-M10F-50-TE-3N




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5F-07-TI




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5F-07-TI-NR




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5F-08-SE




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5F-10-TI




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5F-15-TI




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5F-20-TI




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5M-10-TE




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-M5M-20-TE




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-NFA-06-TI




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-NFA-10-TI



- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-NFA-25-TI-NR




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

彈簧推杆


ZLC 系列

ZLC-NFB-05-SI-NR




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-NFB-06-TI




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-NFB-10-TI




- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-NFC-06-TI



- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口

ZLC-NFC-10-TI



- ① 固定
- ③ 真空接口
- ⑬ 吸唇连接口