

真空发生器 ZPG 系列

▶ 产品优点



▶ 性能强劲

- 体积流量: 85 l/min - 343 l/min
- 空气消耗量: 20 l/min - 194 l/min
- 最大真空度: -94 kPa

▶ 适用于洁净室

外壳采用防污设计。集成式过滤器具有自清洁功能，可减少维护次数，提高效率。

▶ 产品代码

ZPG	20	31	F	W
系列	真空气类型	真空气的级数与数量	真空气过滤器	外壳颜色


▶ 技术数据

▶ 技术数据


定购编号	最大真空度 [kPa]	体积流量 [l/min]	4 bar 压力下的空气消耗量 [l/min]	5.5 bar 压力下的空气消耗量 [l/min]	真空气过滤器	最大操作气压 [bar]	重量 [kg]
ZPG2031-F-W	-90	85	32		是	7	0.05
ZPG2032-F-W	-90	172	64		是	7	0.09
ZPG2531-F-W	-94	146		77	是	7	0.1
ZPG2532-F-W	-94	292		154	是	7	0.1
ZPG3021-W	-92	171	152		没有	7	0.11
ZPG3022-W	-92	343	304		没有	7	0.21

► 图表


ZPG2031




ZPG2032



ZPG2531





ZPG2532





真空发生器 ZPG 系列

ZPG3021




ZPG3022



► 技术图纸

ZPG2031-F-W




① 固定

② 压缩空气接口

③ 真空接口

⑤ 排气/排气阀

ZPG2032-F-W




① 固定

② 压缩空气接口

③ 真空接口


⑤ 排气/排气阀

ZPG2531-F-W




- ① 固定
② 压缩空气接口
③ 真空接口
④ 排气/排气阀
⑤ 排气/排气阀

ZPG2532-F-W




ZPG3021-W



- ① 固定
② 压缩空气接口
③ 真空接口
④ 排气/排气阀
⑤ 排气/排气阀

ZPG3022-W



- ① 固定
② 压缩空气接口
③ 真空接口
④ 排气/排气阀
⑤ 排气/排气阀