


# PLUG-IN CONNECTOR STRAIGHT WITH CABLE

## KAG500S4

Order no.	KAG500S4
<b>Technical Data</b>	
Fixing thread	M8
Connection type	Male
Version [Type]	Straight
No. of contacts	4
Rated voltage [V]	60
Current load (at 40°C) [A]	4
Insulation resistance	≥10 <sup>6</sup> Ω
Resistance	≤5mΩ
Contact material	Metal, CuSn, gold-plated
Contact-carrier material	Plastic, TPU, BK
Grip body material	Plastic, TPU, BK
Coupling nut material	Metal, CuZn, nickel-plated
Sealing material	FPM/FKM
Cable sheath material	PUR
Cable length [m]	5
Cable-Ø [mm]	4.7
Nr. of wires x diameter [mm <sup>2</sup> ]	4x0.25
Bend radius	10xØ
Temperature range (fixed) [°C]	-40 ... +90
Temperature range (drag chain) [°C]	-25 ... +60
Rated voltage cable [V]	≤300
Protection to IEC 60529	IP67
Cable end assembly	open cable end
<b>Special features</b>	
Flame retardant	Yes
Seawater resistant	Yes
Recyclable	Yes
LABS-compliant	Yes
RoHS compliant	Yes
Acid- and alkali resistant	Yes
Ozone resistant	Yes
UV resistant	Yes
Hydrolysis proof	Yes
Drag chain-adapted	Yes
Torsion resistant	Yes
Welding sparks resistant	Yes
Halogen-free	Yes
Silicone free	Yes
Oil resistant	Yes

PIN assignment



- |         |         |
|---------|---------|
| ① BROWN | ③ BLUE  |
| ② WHITE | ④ BLACK |

