


SPN ZERO-POINT CLAMPING SYSTEM

SPN112P6 - CLAMPING PLATE

▶ 6-FOLD



- ▶ Compact design with optimized design height
- ▶ System assembly with high precision
- ▶ Integrated air supply/distribution
- ▶ Integrated PLUS connection
- ▶ Available with the advanced zero-point clamping system on request
- ▶ Variable mounting options

▶ Technical Data

Order no.	SPN112P6E6SD-B	SPN112P6E4SD-B
Operation mode	Pneumatic	Pneumatic
Holding force max.	6xM10/M12	6xM10/M12
Operating pressure [bar]	6 ... 7	4 ... 7
Pull-in force [kN]	6.0	4.0
Pull-in force with PLUS connection [kN]	6x15	6x10
Operating temperature [°C]	-10 ... +70	-10 ... +70
Rotation prevention	Yes	Yes
PLUS connection	Yes	Yes
Air cleaning	No	No
Piston position sensing	No	No
Contact monitoring	No	No
Material	Tempered stainless steel/steel	Tempered stainless steel/steel
Weight [kg]	59	58

