


ENERGY ELEMENT

WER4000LFL01-13-A

Order no.	WER4000LFL01-13-A
Series	WER4000
Transmission mode	fluidic
Compatible with installation size	WWR1160 / WWR1200
Compatible with	Loose part
Number of fluid couplings	1
Fixing thread	G1/2"
Operating pressure max. [bar]	250
Coupling pressure max. [bar]	10
Nominal diameter	8
Flow per connector max. [l/min]	25
Connection alignment	radial
Joining force [N]	100
Protection to IEC 60529	IP54*
Weight [kg]	0.67

* only in coupled state

► Coupling force per fluid coupling



► Flow

