ZiMo - THE MOBILE ROBOT

PRODUCTIVE FROM DAY 1

THE CHALLENGES

The ongoing shortage of skilled workers is creating organizational challenges for many companies and causing significant costs. Shortages in staff lead to production delays, quality losses and restricted growth.

- ➤ Shortage of skilled workers monotonous manual labor is difficult to fill
- High flexibility requirements changing orders and small batch sizes
- ▶ Machine downtimes staff shortages cause downtimes
- Loss of quality overworking skilled workers leads to errors



THE SOLUTION – ZIMO AUTOMATION THAT ANYONE CAN OPERATE

Ready for use 24/7

Reliable 24/7 – for maximum utilization of capacity and consistently high efficiency, even in three-shift operation.

Bridge the shortage of skilled workers

Automated processes take the pressure off your team and secure production, even when you are short-staffed.

Maximum performance with maximum security

Smart safety components for smooth operation without compromising on cycle time, flexibility or quality.



Ideal for small and varying batch sizes



Increased productivity



Flexible use



Optimized production processes




Customizable




Fast return on investment (ROI)

FAST RETURN ON INVESTMENT

With ZiMo, automation becomes the strategic answer to industrial challenges: More orders in less time and lower costs for personnel, operating and maintenance increase efficiency and revenue. This enables you to remain competitive and benefit from a fast ROI while also achieving sustainable cost savings.









ZiMo - THE MOBILE ROBOT

TECHNICAL DETAILS



Base module

- Base frame on four lifting rollers with locking feet
- Partially machined tabletop
- Control cabinet including fan / ventilation grille
- Prepared interface (pneumatic/electric)
- Basic electrical equipment
- Status display (LED strip)
- Docking bar with "present" query
- Integrated brackets for accessories



Engineering and services

For mechanics, optional PLC support

Complete end effector portfolio (configurable)

Pneumatic, electric, vacuum

Options (configurable)

- Safety scanner, Storage station for MATCH components
- Interfaces (Digital Safety I/O, Euromap 67, passive distributor, IO-Link, pneumatics)
- SLC rack and extra docking bars

APPLICATIONS

Pick & Place

- Workpiece removal
- Workpiece handling
- Collaborative installation
- Quality assurance (De)palletizing
- Packaging

GO TO ZIMO

	► Technical data
ZiMo	
Control system visualization	Customized
Weight [kg]	305
Length [mm]	720
Width [mm]	920
Min./max. operating temperature [°C]	+5 +40
Electrical connection	Plug CEE 16 A, 400 V, 5-pin

	► Technical data				
Robots / FANUC	CRX-5iA	CRX-10iA	CRX-10iA/L	CRX-20iA/L	
Range [mm]	994	1249	1418	1418	
Max. load capacity [kg]	5	10	10	20	
Certificates	EN ISO 13849-1, Performance level d of category 3 and EN ISO 10218-1				
Robot control system	R-30iB mini plus	R-30iB mini plus	R-30iB mini plus	R-30iB plus	
Max. TCP speed [m/s]	2	2	2	1	
Position repeat accuracy [mm]	± 0.03	± 0.04	± 0.04	± 0.04	

HEADQUARTERS: ZIMMER GROUP

Am Glockenloch 2 77866 Rheinau, Germany T +49 7844 9139-0 F +49 7844 9139-1199 info.de@zimmer-group.com www.zimmer-group.com

CONTACT - WORLDWIDE

With our current 19 global subsidiaries and partners in over 125 countries, we offer the excellent service of a technology leader. We look forward to hearing from you!

Order no. MKT000115-02