

STORAGE STATION


ALSR13160

PRODUCT SPECIFICATIONS



Forces and moments



Shows static forces and torques that may have an effect on the storage station due to the loose part



Mr [Nm]	50
Mx [Nm]	120
My [Nm]	200
Fa_H [N]	1500
Fa_V [N]	750



Horizontal design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Y directions



Vertical design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Z directions



RECOMMENDED ACCESSORIES



SENSORS



NJ8-E2
Inductive proximity switch - Cable 5 m



SENSORS



NJ8-E2S
Inductive proximity switch, M8



Order no.	► Technical Data
Compatible with installation size	ALSR13160
Approvals	WWR160L-B
Weight [kg]	LABS / REACH / RoHS
	13

- ⑦ Intake for proximity switch
- ⑤① Fixing loose part
- ⑧ Fixing ALSR

