


STORAGE STATION


AWPR5080-00-A

PRODUCT SPECIFICATIONS



Forces and moments



Shows static forces and torques that may have an effect on the storage station due to the loose part



Mr [Nm]	140
Mx [Nm]	120
My [Nm]	140
Fa_H [N]	1000
Fa_V [N]	1000

Horizontal design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Y directions



RECOMMENDED ACCESSORIES



SENSORS



NJR04-E2SK
Inductive Proximity Switch Cable 0,3 m - Connector M8

► Technical Data	
Order no.	AWPR5080-00-A
Compatible with	WPR5080L-00-A
Weight [kg]	0.44

- ⑦ Intake proximity switch
- ⑤① Fixing loose part
- ⑦③ Possible stroke for extending
- ⑦⑥ Fastening AWPR

