

STORAGE STATION


ALSR1-63-B

PRODUCT SPECIFICATIONS



Forces and moments



Shows static forces and torques that may have an effect on the storage station due to the loose part



Mr [Nm]	4
Mx [Nm]	8
My [Nm]	15
Fa_H [N]	250
Fa_V [N]	125



Horizontal design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Y directions



Vertical design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Z directions



RECOMMENDED ACCESSORIES



SENSORS



NJ8-E2
Inductive proximity switch - Cable 5 m



SENSORS



NJ8-E2S
Inductive proximity switch - Connector M8



Order no.	Technical Data
Compatible with installation size	ALSR1-63-B
Weight [kg]	WWR63L-B
	1.9

- ⑦ Intake for proximity switch
- ⑤① Fixing loose part
- ①① Fixing ALSR

