


STORAGE STATION


AWPR5100-00-A

PRODUCT SPECIFICATIONS





Forces and moments

Shows the maximum forces and moments which may impact on the storage station due to the loose part



Mr [Nm]	600
Mx [Nm]	500
My [Nm]	600
Fa_H [N]	3000
Fa_V [N]	3000

Horizontal design



RECOMMENDED ACCESSORIES



SENSORS



NJR04-E2SK
Inductive Proximity Switch Cable 0,3 m - Connector M8



► Technical Data	
Order no.	AWPR5100-00-A
Compatible with	WPR5100L-00-A
Certifications	LABS / REACH / RoHS
Weight [kg]	0.91

- ⑦ Intake proximity switch
- ⑤① Fastening loose part
- ⑦③ Possible stroke for extending
- ⑦⑥ Fastening AWPR
- ⑧① Fastening sensor actuator

