


스토리지 스테이션


AWPR5200-10-A

▶ 제품 규격





▶ 힘 및 모멘트

이 부품으로 인해 적재 스테이션에 가해질 수 있는 최대 힘과 모멘트를 나타냅니다.





Mr [Nm]	1200
Mx [Nm]	1200
My [Nm]	1200
Fa_H [N]	12000
Fa_V [N]	12000

▶ 수평 구조



▶ 수직 구조



▶ 부품 권장



에너지 공급



WV1-8X6
각선화-나사 체결부



센서



NJ3-E2SK
직선 케이블 0.3 m - 소켓 M8 플러그 연결



센서



NJR04-E2SK
직선 케이블 0.3 m - 소켓 M8 플러그 연결



연결/기타



ZUB123084
스트레인 릴리프

주문번호	기술 데이터
적합	AWPR5200-10-A
축 X/Y-평면 +/- [mm]	WPR5200L-00-A
인증	0.75
무게 [kg]	LABS / REACH / RoHS
	9.9

