


STORAGE STATION


AWPR5200-10-A

PRODUCT SPECIFICATIONS



Forces and moments



Shows the maximum forces and moments which may impact on the storage station due to the loose part



Mr [Nm]	1200
Mx [Nm]	1200
My [Nm]	1200
Fa_H [N]	12000
Fa_V [N]	12000


Horizontal design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Y directions



Vertical design

Shows the maximum handling weight depending on the center distances of the center of gravity in the X and Z directions



RECOMMENDED ACCESSORIES



ENERGY SUPPLY



WW1-8X6
Angled Fittings - Quick Connect Style



SENSORS



NJ3-E2SK
Inductive Proximity Switch Cable 0,3 m - Connector M8



SENSORS



NJR04-E2SK
Inductive Proximity Switch Cable 0,3 m - Connector M8



CONNECTIONS / OTHER



ZUB123084
Strain relief

► Technical Data	
Order no.	AWPR5200-10-A
Compatible with	WPR5200L-00-A
Compensation X/Y level +/- [mm]	0.75
Certifications	LABS / REACH / RoHS
Weight [kg]	9.9

