# **3-JAW CONCENTRIC GRIPPERS SERIES GD300**

#### PRODUCT ADVANTAGES



#### "The economical"

#### Concentration on the essentials

The most economic type of gripping: This is how you reduce your production costs

#### Proven T slot guide

This established and proven guiding technology stands for the highest process reliability like no other

#### Compact structure


Reduces the interference contours for your application

### > SERIES CHARACTERISTICS

Installation size	Version					
GD3XX	N	NC	NO	S	SC	SO
Spring closing C		•			•	
Spring opening O			•			•
High-strength S				•	•	•
10 million maintenance-free cycles (max.)	•	•	•	•	•	•
+ multiple inductive sensor	•	•	•	•	•	•
+ Magnetic field sensor	•	•	•	•	•	•
Purged air	•	•	•	•	•	•
IP 40 IP40	•	•	•	•	•	•



#### **BENEFITS IN DETAIL**



- 1 Robust, lightweight housing
  - Hard-coated aluminum alloy
- 2 Energy supply
  - possible from several sides
- 3 Mounting and positioning
  - mounting possible from several sides for versatile positioning
- 4 Gripper jaw
  - individual gripper finger mounting
- 5 Wedge hook mechanism
  - synchronized the movement of the gripper jaws
  - high force transfer
- (6) Integrated gripping force safety device
  - spring integrated into cylinder as energy storage
- 7 Position sensing
  - permanent magnet for direct monitoring of piston movement
- 8 Integrated, adjustable switch cam
  - for direct position sensing of the gripper jaw
- 9 Mounting block
  - mounting for inductive proximity switch (10)

# ► TECHNICAL DATA

	Stroke per jaw	Gripping force	Weight	IP class
Installation size	[mm]	[N]	[kg]	
GD303	3	200 - 300	0,13 - 0,16	IP40
GD304	2 - 4	450 - 1500	0,22 - 0,28	IP40
GD306	3 - 6	750 - 2300	0,5 - 0,65	IP40
GD308	4 - 8	1200 - 4000	0,85 - 1,2	IP40
GD310	5 - 10	2000 - 6400	1,6 - 2,2	IP40
GD312	6 - 12	3500 - 9250	2,7 - 3,8	IP40
GD316	8 - 16	6500 - 19100	5,1 - 8	IP40
GD320	10 - 20	8200 - 18700	9,6	IP40
GD330	15 - 30	15300 - 34700	24	IP40

#### ► FURTHER INFORMATION IS AVAILABLE ONLINE



All information just a click away at: <a href="www.zimmer-group.com">www.zimmer-group.com</a>. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.

# 3-JAW CONCENTRIC GRIPPERS **INSTALLATION SIZE GD303**

#### PRODUCT SPECIFICATIONS



#### Gripping force diagram

[N] Shows the arithmetic total of the individual forces that occur on the gripper fingers, depending on the gripper finger length 300 240 O GD303NC-C 180 GD303NO-C ♦GD303N-C -><-◆166661 N 120 [mm] Colored area: increased wear and tear to be expected

#### Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.



Mr [Nm]	6
Mx [Nm]	9
My [Nm]	12
Fa [N]	500

#### ► INCLUDED IN DELIVERY



2 [piece] Mounting block KB3-07



6 [piece] Centering Disc DST40400

### RECOMMENDED ACCESSORIES



# **GRIPPING COMPONENTS**



#### **UB303**

Universal jaw set aluminium



# **SENSORS**



#### NJ3-E2SK

Inductive Proximity Switch Cable 0,3 m - Connector M8





#### UB303ST

Universal jaw set steel



#### MFS01-S-KHC-P1-PNP

Magnetic field sensor angled, cable 0.3 m - M8 connector





### **ENERGY SUPPLY**



### MFS02-S-KHC-P1-PNP

Magnetic field sensor straight, cable 0.3 m - M8 connector





#### GVM5

Straight Fittings - Quick Connect Style



#### MFS02-S-KHC-IL

Position sensor straight, cable 0.3 m - connector





#### WVM5

Angled Fittings - Quick Connect Style



# **CONNECTIONS / OTHER**



Plug-in connector Straight Cable 5m - Socket M8 (female)





#### DSV1-8E

DSV1-8

Pressure safety valve

Pressure safety valve with quick exhaust




#### KAW500

Plug-in connector Angled Cable 5m - Socket M8 (female)



	Technical data		
Order no.	GD303N-C	GD303NC-C	GD303NO-C
Stroke per jaw [mm]	3	3	3
Gripping force in closing [N]	200	270	
Gripping force in opening [N]	230		300
Gripping force secured by spring min. [N]		70	70
Closing time [s]	0.02	0.02	0.03
Opening time [s]	0.02	0.03	0.02
Repetition accuracy +/- [mm]	0.05	0.05	0.05
Operating pressure min. [bar]	2	4	4
Operating pressure max. [bar]	8	8	8
Nominal operating pressure [bar]	6	6	6
Operating temperature min. [°C]	+5	+5	+5
Operating temperature max. [°C]	+80	+80	+80
Air volume per cycle [cm³]	3.5	6.7	6.7
Protection to IEC 60529	IP40	IP40	IP40
Weight [kg]	0.14	0.15	0.16






# **3-JAW CONCENTRIC GRIPPERS SERIES GD300 FUNCTIONAL DESCRIPTION**




### **GRIPPING COMPONENTS**



#### Universal jaws - UB300


When the gripper fingers are open, the pressure piece is used for spring-supported positioning of the workpiece against a limit stop. This greatly reduces the loads on the gripper that arise during joining.




#### Pressure piece - ADS300

When the gripper fingers are open, the pressure piece is used for spring-supported positioning of the workpiece against a limit stop. This greatly reduces the loads on the gripper that arise during joining.








#### **Pneumatic threaded connections**

Available in straight and angled design. Can be chosen freely depending on the space conditions or installation situation.




#### Pressure safety valve - DSV


Ensures safe retention of force and position if the system pressure drops

The integrated double check valve, which can be unlocked, retains the system pressure of the gripper in case of EMERGENCY STOP. To ensure the function, the valve must be installed as close to the gripper's air connection as possible. In variant E, two pushbuttons are installed that allow for controlled bleeding of the gripper.

# **3-JAW CONCENTRIC GRIPPERS SERIES GD300 FUNCTIONAL DESCRIPTION**









#### Inductive sensors - NJ

The sensor is inserted into the mounting block as far as it will go and secured. Tuning to the desired position then takes place by adjusting the cam switch. The sensors are available in versions with 5 m cables with exposed leads and 0,3 m cable with connector, as well as with direct plug orientation.




MFS02





MFS01



#### 1-point magnetic field sensors - MFS

For non-contact sensing of the piston position

These sensors are installed in the C-groove of the gripper and detect the magnet attached to the piston of the gripper. To ensure use in a wide variety of space conditions, the sensors are available in two variants. While the horizontal MFS02, with straight cable outlet, disappears into the C-groove of the gripper almost completely, the vertical MFS01 is taller, but has a cable outlet that is offset at an angle of 90°. The variants are available in versions with 5 m cables with exposed leads and 0,3 m cable with connector.

# **3-JAW CONCENTRIC GRIPPERS SERIES GD300 FUNCTIONAL DESCRIPTION**




# **CONNECTIONS / OTHER**



### **Plug-in connectors**

For extending and fabricating the connection lines

Cables with a length of 10 m with exposed leads are available. Depending on the specific needs, the cables can be shortened or fabricated with connectors in sizes M12. A 5 m long cable with connector / socket is available for the IO-Link connection.



#### **Centering sleeves**

For defined position measurement of the gripper fingers

The centering sleeves are inserted into the fits of the gripper jaws to define the position of the gripper fingers. The centering sleeves are comparable to a pin connection.