


3-JAW CONCENTRIC GRIPPERS

INSTALLATION SIZE GED1502

▶ PRODUCT SPECIFICATIONS




▶ Gripping force diagram



▶ Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.



Mr	4
Mx	5
My	4
Fa	200

▶ INCLUDED IN DELIVERY



Centering Disc


DST02900



Control


ELEGR01

▶ RECOMMENDED ACCESSORIES



Plug-in connector Angled
Cable 5m - Socket M8
(female)

KAW500



Plug-in connector Straight
Cable 5m - Socket M8
(female)

KAG500

► Technical Data	
Order no.	GED1502
Stroke per jaw [mm]	2
Gripping force in closing (adjustable) max. [N]	115
Gripping force in opening (adjustable) max. [N]	115
Closing time [s]	0.2
Opening time [s]	0.2
Repetition accuracy +/- [mm]	0.02
Voltage [V]*	24
Max. current regulable by potentiometer [mA]	140
Operating temperature min. [°C]	5
Operating temperature max. [°C]	80
Protection to IEC 60529	IP67
Weight [kg]	0.32

*12 volt voltage on request

