
2-JAW PARALLEL GRIPPERS SERIES GP200

PRODUCT ADVANTAGES



"The variable"

Smooth stroke configuration

An adjusting screw allows you to adjust the stroke to your specific application

Proven technology

We have more than 20 years of proven reliability, which ensures uninterrupted production for you

Dirt protection


Using the scrapers on the guides, you can reliably use the gripper even under the harshest conditions

SERIES CHARACTERISTICS

Installation size		Ver	sion	
GP2XX	-	-99	S	S-99
Spring closing C	•		•	
F High-strength S			•	•
10 million maintenance-free cycles (max.)	•	•	•	•
+ 💭 Inductive sensor	•	•	•	•
Magnetic field sensor	•	•	•	•
Purged air	•	•	•	•
IP 40 IP40	•	•	•	•

F

BENEFITS IN DETAIL



1 Stroke adjustment

infinitely adjustable in "open" movement adjusting screw in delivery

Wedge hook mechanism
synchronized the movement of the gripper jaws
high force transfer

3 Square guide

- high forces and moments capacity

(4) Gripper jaw

- individual gripper finger mounting

5 Mounting and positioning

- mounting possible from several sides for versatile positioning

6 Sensing slot

- mounting and positioning of magnetic field sensors

7 Drive

- double-acting pneumatic cylinder

8 Energy supply

- possible from several sides

TECHNICAL DATA

	Stroke per jaw	Gripping force Weight		IP class
Installation size	[mm]	[N]	[kg]	
GP224	6 - 12	170 - 335	0,33	IP40
GP240	8 - 20	510 - 1290	1,2	IP40
GP260	10 - 30	800 - 2480	2,9	IP40
GP280	15 - 40	1690 - 4500	8,3	IP40

FURTHER INFORMATION IS AVAILABLE ONLINE



All information just a click away at: www.zimmer-group.com. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.

2-JAW PARALLEL GRIPPERS INSTALLATION SIZE GP240

PRODUCT SPECIFICATIONS



	Technical data				
Order no.	GP240-B	GP240-B-99	GP240S-B	GP240S-B-99	
Stroke per jaw [mm]	20	20	8	8	
Gripping force in closing [N]	510	435	1290	1105	
Gripping force in opening [N]		435		1105	
Gripping force secured by spring min. [N]	75		185		
Closing time [s]	0.1	0.08	0.1	0.08	
Opening time [s]	0.1	0.08	0.1	0.08	
Repetition accuracy +/- [mm]	0.05	0.05	0.05	0.05	
Operating pressure min. [bar]	5	3	5	3	
Operating pressure max. [bar]	8	8	8	8	
Nominal operating pressure [bar]	6	6	6	6	
Operating temperature min. [°C]	+5	+5	+5	+5	
Operating temperature max. [°C]	+80	+80	+80	+80	
Air volume per cycle [cm ³]	49	49	49	49	
Protection to IEC 60529	IP40	IP40	IP40	IP40	
Weight [kg]	1.3	1.2	1.2	1.2	

