


适用于特殊任务的抓手

安装尺寸 GFP2012


产品规格




夹持力图表



夹持力图表



随货提供



中心定位环

DST41000



无头螺丝

NAB07390

力和力矩

显示除夹持力外可能作用的静力和力矩。




Mr	35
Mx	50
My	42
Fa	1400

配件建议



通用手指

UB2012



盖片套装

ADB2012



钩型扳手

ZUB0004

订购编号	▶ 技术数据			
	GFP2012NC-14	GFP2012NC-16	GFP2012NC-25	GFP2012NC-34
刀座	HSK-A63	HSK-A100	VDI 40	Capto C6
单边行程 [mm]	12	12	12	12
最小闭合抓取力(可调节) [N]	460	460	460	460
最大闭合抓取力(可调节) [N]	1140	1140	1140	1140
最小操作气压 [bar]	10	10	10	10
最大操作气压 [bar]	50	50	50	50
最小操作温度 [°C]	+5	+5	+5	+5
最高操作温度 [°C]	+80	+80	+80	+80
重量 [kg]	5.4	5.4	5.4	5.4

