


2-JAW RADIAL GRIPPER

SERIES GG4000

▶ PRODUCT ADVANTAGES



“The sealed”

▶ Suitable for use under extreme conditions

The sealed rotation axis guarantees process reliability even under the harshest conditions

▶ Smooth stroke configuration

You can adjust the 180° opening angle to be unique to your application using an adjusting screw

▶ Failure-free continuous operation


Our uncompromising “Made in Germany” quality guarantees up to 10 million maintenance-free cycles

▶ SERIES CHARACTERISTICS

Installation size	Version	
GG40XX-B	NC	SC
 Spring closing C	•	•
 High-strength S		•
 10 million maintenance-free cycles (max.)	•	•
 Inductive sensor	•	•
 Magnetic field sensor	•	•
 Protected against corrosion	•	•
 Purged air	•	•
 IP 64	•	•



► BENEFITS IN DETAIL



- ① **Stroke adjustment screw**
- Infinitely adjustable opening stroke
- ② **Removable centering sleeves**
- individual gripper finger mounting
- ③ **Robust, lightweight housing**
- Hard-coated aluminum alloy
- ④ **Sensing slot**
- mounting and positioning of magnetic field sensors
- ⑤ **Mounting and positioning**
- mounting possible from several sides for versatile positioning
- ⑥ **Integrated gripping force safety device**
- spring integrated into cylinder as energy storage
- ⑦ **Position sensing**
- permanent magnet for direct monitoring of piston movement
- ⑧ **Mounting block**
- mounting for inductive proximity switch
- ⑨ **Sealed rotation point**
- for use under extreme conditions

► TECHNICAL DATA

Installation size	Stroke per jaw (+/-) [°]	Gripping force [N]	Weight [kg]	IP class
GG4032	20 - 90	430 - 460	0,25	IP64
GG4040	20 - 90	700 - 800	0,5	IP64
GG4049	20 - 90	1000 - 1150	0,85	IP64
GG4058	20 - 90	1650 - 1900	1,4	IP64
GG4072	20 - 90	1950 - 2700	2,45	IP64
GG4084	20 - 90	3500 - 4000	4,5	IP64

► FURTHER INFORMATION IS AVAILABLE ONLINE



All information just a click away at: www.zimmer-group.com. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.


2-JAW RADIAL GRIPPER

INSTALLATION SIZE GG4058

PRODUCT SPECIFICATIONS




Gripping force diagram



Forces and moments


Displays static forces and moments that can also have an effect, besides the gripping force.



Mr [Nm]	33
My [Nm]	33
Fa [N]	720


Moment of inertia

GG4058NC-B



Moment of inertia

GG4058SC-B



INCLUDED IN DELIVERY



4 [piece]
Centering Disc
DST11500



2 [piece]
Flow Control Valves - with Swivel joint
DRVM5X4

RECOMMENDED ACCESSORIES



ENERGY SUPPLY



DSV1-8E
Pressure safety valve with quick exhaust



SENSORS



MFS02-S-KHC-P1-PNP
Magnetic field sensor straight, cable 0.3 m - M8 connector



SENSORS



KB8-49
Mounting block



MFS01-S-KHC-P2-PNP
2-point sensor angled, cable 0.3 m - M8 connector



MFS02-S-KHC-P2-PNP
2-point sensor straight, cable 0.3 m - M8 connector



NJ8-E2S
Inductive proximity switch - M8



MFS02-S-KHC-IL
Straight position sensor, cable 0.3 m - M8 plug



MFS01-S-KHC-P1-PNP
Magnetic field sensor angled, cable 0.3 m - M8 connector



Order no.	► Technical data	
	GG4058NC-B	GG4058SC-B
Stroke per jaw [°]	90	20
Gripping moment in closing at 0° [Nm]	46	53.5
Gripping moment secured by spring min. [Nm]	7	15
Gripping force in closing at 0° [N]	1650	1900
Dead weight of mounted gripper finger max. [kg]	0.36	0.36
Length of the gripper fingers max. [mm]	120	120
Closing time [s]	0.16	0.08
Opening time [s]	0.28	0.17
Repetition accuracy +/- [mm]	0.05	0.05
Operating pressure min. [bar]	4	4
Operating pressure max. [bar]	8	8
Nominal operating pressure [bar]	6	6
Operating temperature min. [°C]	5	5
Operating temperature max. [°C]	+80	+80
Air volume per cycle [cm³]	86	65
Certifications	LABS / REACH / RoHS	LABS / REACH / RoHS
Protection to IEC 60529	IP64	IP64
Weight [kg]	1.4	1.4

