# 2-JAW RADIAL GRIPPER **SERIES GG4000**

## PRODUCT ADVANTAGES



### "The sealed"

#### Suitable for use under extreme conditions

The sealed rotation axis guarantees process reliability even under the harshest conditions

#### Smooth stroke configuration

You can adjust the 180° opening angle to be unique to your application using an adjusting screw

### ► Failure-free continuous operation


Our uncompromising "Made in Germany" quality guarantees up to 10 million maintenance-free cycles

# > SERIES CHARACTERISTICS

Installation size	Version	
GG40XX-B	NC	SC
Spring closing C	•	•
High-strength S		•
10 million maintenance-free cycles (max.)	•	•
+ multiple sensor	•	•
+ Magnetic field sensor	•	•
Protected against corrosion	•	•
Purged air	•	•
IP 64 IP64	•	•



# **BENEFITS IN DETAIL**



- 1 Stroke adjustment screw
  - Infinitely adjustable opening stroke
- 2 Removable centering sleeves
  - individual gripper finger mounting
- 3 Robust, lightweight housing
  - Hard-coated aluminum alloy
- 4 Sensing slot
  - mounting and positioning of magnetic field sensors
- 5 Mounting and positioning
  - mounting possible from several sides for versatile positioning
- 6 Integrated gripping force safety device
  - spring integrated into cylinder as energy storage
- 7 Position sensing
  - permanent magnet for direct monitoring of piston movement
- 8 Mounting block
  - mounting for inductive proximity switch
- 9 Sealed rotation point
  - for use under extreme conditions

# **► TECHNICAL DATA**

	Stroke per jaw (+/-)	Gripping force	Weight	IP class
Installation size	[°]	[N]	[kg]	
GG4032	20 - 90	430 - 460	0,25	IP64
GG4040	20 - 90	700 - 800	0,5	IP64
GG4049	20 - 90	1000 - 1150	0,85	IP64
GG4058	20 - 90	1650 - 1900	1,4	IP64
GG4072	20 - 90	1950 - 2700	2,45	IP64
GG4084	20 - 90	3500 - 4000	4,5	IP64

### ► FURTHER INFORMATION IS AVAILABLE ONLINE




All information just a click away at: www.zimmer-group.com. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.

# 2-JAW RADIAL GRIPPER **INSTALLATION SIZE GG4058**

# PRODUCT SPECIFICATIONS



#### **Gripping force diagram**




#### Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.




Mr [Nm]	33
My [Nm]	33
Fa [N]	720

# Moment of inertia GG4058NC-B



# Moment of inertia GG4058SC-B



# INCLUDED IN DELIVERY



4 [piece] DST11500



2 [piece]

Flow Control Valves - with Swivel joint

DRVM5X4

# RECOMMENDED ACCESSORIES



# **ENERGY SUPPLY**



#### DSV1-8E

Pressure safety valve with quick exhaust




**SENSORS** 

MFS02-S-KHC-P1-PNP Magnetic field sensor straight, cable 0.3 m - M8 connector



# **SENSORS**





#### MFS01-S-KHC-P2-PNP

2-point sensor angled, cable 0.3 m - M8 connector





#### KB8-49

Mounting block



#### MFS02-S-KHC-P2-PNP

2-point sensor straight, cable 0.3 m - M8 connector





#### NJ8-E2S

Inductive proximity switch - Connector M8



#### MFS02-S-KHC-IL

Position sensor straight, cable 0.3 m - connector





#### MFS01-S-KHC-P1-PNP

Magnetic field sensor angled, cable 0.3 m - M8 connector



	► Technical data	
Order no.	GG4058NC-B	GG4058SC-B
Stroke per jaw [°]	90	20
Gripping moment in closing at 0° [Nm]	46	53.5
Gripping moment secured by spring min. [Nm]	7	15
Gripping force in closing at 0° [N]	1650	1900
Dead weight of mounted gripper finger max. [kg]	0.36	0.36
Length of the gripper fingers max. [mm]	120	120
Closing time [s]	0.16	0.08
Opening time [s]	0.28	0.17
Repetition accuracy +/- [mm]	0.05	0.05
Operating pressure min. [bar]	4	4
Operating pressure max. [bar]	8	8
Nominal operating pressure [bar]	6	6
Operating temperature min. [°C]	5	5
Operating temperature max. [°C]	+80	+80
Air volume per cycle [cm³]	86	65
Protection to IEC 60529	IP64	IP64
Weight [kg]	1.4	1.4

