2-JAW PARALLEL GRIPPERS WITH LONG STROKE **SERIES GHK6000**


PRODUCT ADVANTAGES



"The robust"


- Securing the workpiece in case of drop in pressure above clamping element on the condition of a positive gripper jaw design
- ▶ Dimensions based on GH6000 series standard grip-
- Long stroke, up to 200 mm per jaw
- ▶ Stable T-slot guide, guided completely along the entire length of the housing
- For gripper fingers with a length of up to 600 mm
- Compact design, through stacked cylinder and guide

THE BEST PRODUCT FOR YOUR APPLICATION





TECHNICAL DRAWINGS



- ② Air connection
 Min./max. operating pressure: 4/7 bar!
- 4 Air filter

► TECHNICAL DATA

	Retention force in case of drop in pressure	Α	В	С	D	E	F	G
Installation size	[N]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
GHK6140	300	9.6	11.5	21.7	25	17.5	58	22
GHK6160	300	9.6	11.5	21.7	25	37.5	58	22
GHK6180	300	9.6	11.5	21.7	25	57.5	58	22
GHK6240	640	15	14	39.5	35	20	66	27
GHK6260	640	15	14	39.5	35	40	66	27
GHK6280	640	15	14	39.5	35	60	66	27
GHK62100	640	15	14	39.5	35	80	66	27
GHK62150	640	15	14	39.5	35	130	66	27
GHK6360	640	15	14	56	35	47.5	66	27
GHK63100	640	15	14	56	35	87.5	66	27
GHK63150	640	15	14	56	35	137.5	66	27
GHK6460	1050	13.5	20.5	67.4	45	33.5	82	41
GHK64100	1050	13.5	20.5	67.4	45	73.5	82	41
GHK64150	1050	13.5	20.5	67.4	45	123.5	82	41
GHK64200	1050	13.5	20.5	67.4	45	173.5	82	41

► FURTHER INFORMATION IS AVAILABLE ONLINE




All information just a click away at: www.zimmer-group.com. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.

2-JAW PARALLEL GRIPPERS WITH LONG STROKE **INSTALLATION SIZE GH6260**

▶ PRODUCT SPECIFICATIONS





Colored area: increased wear and tear to be expected

Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.



Mr [Nm]	120
Mx [Nm]	150
My [Nm]	100
Fa [N]	3000

► INCLUDED IN DELIVERY



2 [piece] Mounting block

KB8-28



4 [piece] Centering Disc DST41000



2 [piece] Flow Control Valves - with Swivel joint **DRV1-8X8**

> YOU CAN FIND RECOMMENDED ACCESSORIES ON THE FOLLOWING PAGES

	► Technical data				
Order no.	GH6260-B	GHK6260			
Stroke per jaw [mm]	60	60			
Gripping force in closing [N]	1200	1200			
Gripping force in opening [N]	980	980			
Closing time [s]	0.35	0.35			
Opening time [s]	0.35	0.35			
Dead weight of mounted gripper finger max. [kg]	2.5	2.5			
Length of the gripper fingers max. [mm]	250	250			
Repetition accuracy +/- [mm]	0.05	0.05			
Operating pressure min. [bar]	3	3			
Operating pressure max. [bar]	8	8			
Nominal operating pressure [bar]	6	6			
Operating temperature min. [°C]	+5	+5			
Operating temperature max. [°C]	+80	+80			
Air volume per cycle [cm³]	275	275			
Protection to IEC 60529	IP40	IP40			
Weight [kg]	4.1	4.5			

