


2-JAW PARALLEL GRIPPERS

INSTALLATION SIZE GP104

▶ PRODUCT SPECIFICATIONS




▶ Gripping force diagram



▶ Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.



Mr	1
Mx	1
My	1
Fa	120

▶ INCLUDED IN DELIVERY



Mounting block

KB4-03



Centering Disc

DST40400

▶ RECOMMENDED ACCESSORIES



Straight Fittings - Quick Connect Style

GVM5




Inductive proximity switch - Cable 5 m

NJ4-E2



Plug-in connector Angled Cable 5m - Socket M8 (female)

KAW500



Plug-in connector Straight Cable 5m - Socket M8 (female)

KAG500



Universal Jaw Aluminium

UB104



Universal Jaw Steel

UB104ST

Order no.		GP104
Stroke per jaw [mm]		4
Gripping force in closing [N]		84
Gripping force in opening [N]		104
Closing time [s]		0.02
Opening time [s]		0.02
Repetition accuracy +/- [mm]		0.05
Operating pressure min. [bar]		3
Operating pressure max. [bar]		8
Operating temperature min. [°C]		5
Operating temperature max. [°C]		80
Air volume per cycle [cm³]		2
Weight [kg]		0.14

*All data measured at 6 bar

► **Technical Data***

