


2-JAW PARALLEL GRIPPERS

INSTALLATION SIZE GP110

▶ PRODUCT SPECIFICATIONS




▶ Gripping force diagram




▶ Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.



Mr	8
Mx	8
My	8
Fa	250

▶ INCLUDED IN DELIVERY



Mounting block

KB8-25



Centering Disc

BDST40800

▶ RECOMMENDED ACCESSORIES



Straight Fittings - Quick Connect Style

GVM5



Inductive proximity switch - Cable 5 m

NJ8-E2



Inductive proximity switch - Connector M8

NJ8-E2S



Plug-in connector Angled Cable 5m - Socket M8 (female)

KAW500



Plug-in connector Straight Cable 5m - Socket M8 (female)

KAG500



Universal Jaw Aluminium

UB110P



Universal Jaw Steel

UB110PST

Order no.	
Stroke per jaw [mm]	10
Gripping force in closing [N]	380
Gripping force in opening [N]	430
Closing time [s]	0.04
Opening time [s]	0.04
Repetition accuracy +/- [mm]	0.05
Operating pressure min. [bar]	3
Operating pressure max. [bar]	8
Operating temperature min. [°C]	5
Operating temperature max. [°C]	80
Air volume per cycle [cm³]	17
Weight [kg]	0.9

► **Technical Data***

GP110

*All data measured at 6 bar

