3-JAW CONCENTRIC GRIPPERS SERIES GPD5000IL

PRODUCT ADVANTAGES



"The hybrid"

- Pneumatic drive combined with IO-Link technology
- ▶ Up to 50% reduction in cycle times and up to 90% less compressed air usage
- ► Connection over just one pneumatic line and IO-Link
- Integrated valve technology, sensor technology, status display, pressure monitoring and temperature monitoring
- ▶ Part detection down to +/- 0.05 mm for a tolerance range that can be taught for any value
- > 32 workpieces data sets can be programmed
- Protected from corrosion and sealed in accordance with IP64
- ▶ Up to 30 million cycles without maintenance


SERIES CHARACTERISTICS

reddot design award winner 2018

Installation size	Version					
GPD50XXIL	N	NC	NO	S	SC	SO
♦ IO -Link	•	•	•	•	•	•
Spring closing C		•			•	
Spring opening O			•			•
F) High-strength S				•	•	•
30 million maintenance-free cycles (max.)	•	•	•	•	•	•
Integrated sensing	•	•	•	•	•	•
Integrated valve technology	•	•	•	•	•	•
Protected against corrosion	•	•	•	•	•	•
Purged air	•	•	•	•	•	•
IP 64 IP64	•	•	•	•	•	•



BENEFITS IN DETAIL



1 Wedge hook mechanism

- high forces and moments capacity
- Synchronized gripper jaw movement

2 Gripper jaw

- Gripper fingers mounted using removable centering sleeves
- Lubricated for life via incorporated lubrication slots

3 Steel Linear Guide

- Steel in steel guide
- Enables use of extremely long gripper fingers

4 Dual lip seal

- IP64
- Prevents grease from being squeezed out, increasing service life

5 Integrated gripping force safety device

- Spring built into cylinder chamber as an energy store

6 Mounting and positioning

- Alternatively, on several sides for customized mounting

7 Position sensing

- integrated Hallsensor

8 Integrated valve technology

- Activation of the gripper by means of a compressed air supply

9 Integrated control module

- Single-cable solution via IO-Link
- Pressure, temperature, position and other parameters are readable

TECHNICAL DATA

	Stroke per jaw	Gripping force	Weight	IP class	
Installation size	[mm]	[N]	[kg]		
GPD5006IL	3 - 6	740 - 2370	0,75 - 0,85	IP64	
GPD5008IL	4 - 8	1260 - 3910	1,25 - 1,45	IP64	
GPD5010IL	5 - 10	2290 - 7160	2,1 - 2,5	IP64	
GPD5013IL	6 - 13	3770 - 11450	4,4 - 5,3	IP64	
GPD5016IL	8 - 16	6870 - 20330	8,3 - 9,8	IP64	
GPD5025IL	14 - 25	8430 - 22850	14,9 - 18,6	IP64	

► FURTHER INFORMATION IS AVAILABLE ONLINE




All information just a click away at: www.zimmer-group.com. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.

3-JAW CONCENTRIC GRIPPERS INSTALLATION SIZE GPD5013IL

► PRODUCT SPECIFICATIONS



Gripping force diagram



Forces and moments

Displays static forces and moments that can also have an effect, besides the gripping force.





Mr [Nm]	110
Mx [Nm]	150
My [Nm]	130
Fa [N]	3300

► TECHNICAL DATA

Technical data						
Order no.	GPD5013N-IL-10-A	GPD5013NC-IL-10-A	GPD5013NO-IL-10-A	GPD5013S-IL-10-A	GPD5013SC-IL-10-A	GPD5013SO-IL-10-A
Control	② IO -Link	O IO-Link	O IO-Link	O IO-Link	O IO-Link	O IO-Link
Stroke per jaw [mm]	13	13	13	6	6	6
Gripping force in closing [N]	3770	5060		8310	11160	
Gripping force in opening [N]	3910		5200	8600		11450
Gripping force secured by spring min. [N]		1290	1290		2850	2850
Cycle count max. [cycle/min]	210	150	150	210	150	150
Dead weight of mounted gripper finger max. [kg]	2.4	2.4	2.4	2.4	2.4	2.4
Length of the gripper fingers max. [mm]	200	185	185	185	170	170
Repetition accuracy +/- [mm]	0.01	0.01	0.01	0.01	0.01	0.01
Operating pressure min. [bar]	3	4	4	3	4	4
Operating pressure max. [bar]	8	7	7	8	7	7
Nominal operating pressure [bar]	6	6	6	6	6	6
Operating temperature [°C]	+5 +50	+5 +50	+5 +50	+5 +50	+5 +50	+5 +50
Air volume per cycle [cm³]	230	415	415	230	415	415
Integrated valve technology	Yes	Yes	Yes	Yes	Yes	Yes
Integrated position sensing	Yes	Yes	Yes	Yes	Yes	Yes
Voltage [V]	24	24	24	24	24	24
Current consumption max. [A]	0.12	0.12	0.12	0.12	0.12	0.12
Protection to IEC 60529	IP64	IP64	IP64	IP64	IP64	IP64
Weight [kg]	4.6	5.4	5.4	4.7	5.5	5.5

► TECHNICAL DRAWINGS





- 1 Gripper attachment
- 2 Energy supply
- 3 Fixing for gripper finger
- (19) Air purge connection option
- ② Ventilation (R+S: In dirty environments, replace filters with actual exhaust hoses and move the exhaust air outlet to a clean environment)
- 35 Attachment option for customer-specific fittings
- 46 Energy supply IO-Link (M12, 5-pole)
- 49 Ground
- 61 Status display



3-JAW CONCENTRIC GRIPPERS INSTALLATION SIZE GPD5013IL

ACCESORIES



► INCLUDED IN DELIVERY



6 [piece] Centering Disc



018187 CFILT00011

► RECOMMENDED ACCESSORIES



GRIPPING COMPONENTS



UB5013AL Universal jaw aluminium



UB5013ST Universal jaw steel



EB5013AL Aluminum adjustment jaw



EB5013ST Steel adjustment jaw



WB5013L Changeable jaw, loosepart-set



WB5013F Changeable jaw, fix-part



ENERGY SUPPLY



GV1-8X8 Straight Fittings - Quick Connect Style



CONNECTIONS / OTHER



KAG500IL Plug-in connector straight 5 m - plug, socket M12




SCM-C-00-00-A Smart Communication Module

3-JAW CONCENTRIC GRIPPERS SERIES GPD5000IL FUNCTIONAL DESCRIPTION




GRIPPING COMPONENTS



Universal jaws - UB5000

Can be used immediately or for individual reprocessing


The gripper blanks are available in aluminum (AL) and steel (ST) versions and are installed directly on the gripper using the screws in the scope of delivery. The fits for the centering sleeves are already in place for this purpose. One universal jaw is required for each gripper jaw.



Adjustment jaws - EB5000

For tool-free adaptation of the gripper range

By manually activating the locking mechanism, which is pre-tensioned by a spring, the adjustment jaw can be moved within a grid of detent notches that has a number scale. Depending on the forces and torques that apply, the adjustment jaws are available in aluminum (AL) and steel (ST) versions. One adjustment jaw is required for each gripper jaw.



Interchangeable jaws - WB5000

Enable fast change of individual gripper fingers


For each gripper jaw, a fixed part and at least one loose part set is needed, depending on the number of gripper fingers to be changed. Manual locking via the Torx wrench included in the scope of delivery of the fixed part can take place from two sides.



THE GRIPPING COMPONENTS CAN BE COMBINED!


The gripper components listed above can be combined with each other and are compatible with the various series of the 5000 gripper family.





Pneumatic threaded connections

Available in straight and angled design. Can be chosen freely depending on the space conditions or installation situation.




Pressure safety valve - DSV

The throttle check valve integrated into the supply air line retains the system pressure in case of EMERGENCY STOP. To ensure the function, the valve must be installed as close to the gripper's air connection as possible. Control voltage and actuator voltage must be maintained for this purpose.

3-JAW CONCENTRIC GRIPPERS SERIES GPD5000IL FUNCTIONAL DESCRIPTION



CONNECTIONS / OTHER




Centering sleeves

For defined position measurement of the gripper fingers


The centering sleeves are inserted into the fits of the gripper jaws to define the position of the gripper fingers. The centering sleeves are comparable to a pin connection.

SECURED CONFIGURATION EXAMPLES GPP5000IL / GPD5000IL SERIES


► GPP5000IL / GPD5000IL (IO-LINK) WIRING TO CONTROL CABINET (BECKHOFF)



► GPP5000IL / GPD5000IL (IO-LINK) WIRING TO CONTROL CABINET (SIEMENS)



► GPP5000IL / GPD5000IL (IO-LINK) WIRING TO IO-LINK MASTER IP67 (BECKHOFF)



► GPP5000IL / GPD5000IL (IO-LINK) WIRING TO IO-LINK MASTER IP67 (SIEMENS)

