

# CLAMPING ELEMENT | MANUAL

## HK2500M

### ► PRODUCT ADVANTAGES



#### ► small construction

For all common miniature profile rail guides


#### ► Tool-free opening and closing (bi-stable)

By turning the knurled screw

#### ► Maintenance free

50,000 static clamping cycles

### ► TECHNICAL DETAILS



#### ① Miniature profile rail guide

- Available for all common miniature profile rail guides

#### ② Stainless knurled screw

- For opening and closing the clamping unit

#### ③ Clamping jaw

- The floating bearingsguarantee symmetrical application of force

#### ④ Housing

### ► INFORMATION ON THE PRODUCTS

#### APPLICATION SCENARIOS

##### ► Assembly aids

##### ► Optical equipment


##### ► Medical equipment

#### FURTHER INFORMATION

##### ► Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).

## ► TECHNICAL DRAWINGS



## ► TECHNICAL DATA

Order no.	HK2500M
Operation	manual
Holding force [N]	300
Theoretical holding force ( $\mu=0,1$ ) [N]	375
B10d value	50,000
Positioning accuracy +/- [mm]	0,02
Operating temperature [°C]	-10 ... +70
Weight [kg]	0.2
Function	Clamping
Condition	N (bistable) remains in current position
Installation direction	from above
Tightening torque [Nm]	2.50
Certifications	LABS / REACH / RoHS

Schematic drawing. General tolerances according to DIN ISO 2768 T1-f/T2-H. Edges according to ISO 13715. Element has no guiding properties. Guidance must be external. The holding force is the maximum force that can be applied in the axial direction. Each clamping and braking element is tested in a 100% inspection before delivery for the specified holding forces on a hardened steel rail with a lightly oiled lubricating layer (ISO-VG 68). The use of other lubricants or rail coatings can influence the coefficient of friction. The operating instructions must be observed before commissioning. We reserve the right to make technical changes in the course of further development. The latest and further data can be found online and in the operating instructions at [www.zimmer-group.com](http://www.zimmer-group.com).