

MOTOR SPINDLES

HF125-002-001

▶ PRODUCT ADVANTAGES



- ▶ **Rated power S1: 9 kW**
- ▶ **Rated torque S1: 7.3 Nm**
- ▶ **Max. speed: 24,000 rpm**
- ▶ Water cooling
- ▶ IO-Link communication
- ▶ Designed as unit carrier
- ▶ Adapted for use in an angle head, for example
- ▶ Hybrid bearings used for maximum performance
- ▶ Ideal for processing wood, plastics, lightweight metal and composites

▶ EQUIPMENT FEATURES



Conus cleanig of tool fixation



IO-Link



Labyrinth seal



Controllable air connectors



Tool fixation monitoring



Sealing air



Speed monitoring



Automatic tool change

▶ OPTIONS



Acceleration sensor



Vector controlled / feedback



Aggregate interface



Robot change unit

▶ ACCESSORIES



Frequency inverter

Page 41



Control units

Page 41



Adapter
Frequency inverter

Page 41



Cooling units/
connector set

Page 42



Power lines

Page 43



Signal lines

Page 43



Robot change unit

Page 46

▶ TECHNICAL DATA

▶ HF125-002-001

Three phase asynchron motor, 4-poles

Nominal output S1 [kW]	9.0
Rated torque S1 [Nm]	7.3
Nominal current S1 [A]	20.0
Nominal speed	11.750
Maximum speed	24,000
Tool interface	HSK-F63
Motor technology	Asynchronous
Number of poles	4
Release unit	Pneumatic
Cooling	Water
Weight [kg]	13

▶ Interface Diagram

	Interface
A	Tool unlocked
E, F	Cooling system inlet and outlet
Hx	Controllable connection
KR	Conus cleaning
SPL	Sealing air
XD1	Power and signal connector
XG2	Signal connector

