


LINEAR CYLINDERS

SERIES LI

▶ PRODUCT ADVANTAGES



▶ Large locating flange

The large mounting surface simplifies your design and allows secure attachment of follow-on tools









▶ Dampened end position

By using PowerStop shock absorbers, you can gently move up to the end positions, increasing the process reliability and durability of your application

▶ Failure-free continuous operation


Our uncompromising “Made in Germany” quality guarantees up to 10 million maintenance-free cycles

▶ SERIES CHARACTERISTICS

Installation size		Version		
LIXX			D	S
	2 way guiding			•
	3 way guiding		•	
	Continuous piston rod		•	
	10 million maintenance-free cycles (max.)	•	•	•
	Inductive sensor	•	•	•
	Elastomer end position damping	•	•	•
	Powerstop end position damping	•	•	•
	IP54	•	•	•



► BENEFITS IN DETAIL



- ① **Guide rod**
- hardened, polished steel shaft
- ② **Mounting block**
- mounting for inductive proximity switch
- ③ **Drive**
- double-acting pneumatic cylinder
- ④ **Energy supply**
- reducing exhaust air is recommended
- ⑤ **End stop confirmation screw**
- direct flange position sensing
- included in scope of delivery
- ⑥ **End position damping**
- with elastomer absorber or patented hydraulic shock absorber
- ⑦ **Piston rod**
- polished, hard chrome plated steel
- continuous in design D
- ⑧ **Intake flange**
- for connection to application-specific adapter plate (to be supplied by the customer)

► TECHNICAL DATA

Installation size	Stroke [mm]	Pressure force max. [N]	Retraction force [N]	Weight [kg]	IP class
LI16	20 - 50	80 - 100	80	0,05 - 0,1	IP54
LI30	15 - 90	200 - 270	200	0,05 - 0,1	IP54
LI40	40 - 300	270 - 450	270	0,05 - 0,3	IP54
LI50	50 - 300	950	950	0,03 - 0,2	IP54

► FURTHER INFORMATION IS AVAILABLE ONLINE



All information just a click away at: www.zimmer-group.com. Find data, illustrations, 3D models and operating instructions for your installation size using the order number for your desired product. Quick, clear and always up-to-date.

LINEAR CYLINDERS


LI30-15 / LI30-30

► PRODUCT SPECIFICATIONS



► Forces and moments

Max allowable static forces and moments.



► RECOMMENDED ACCESSORIES



ENERGY SUPPLY



DRV5X4
Flow Control Valves - with Swivel joint



SENSORS



NJ12-E2S
Inductive proximity switch - Connector M8



CONNECTIONS / OTHER



AP30
Adapter plate



AD-M10X1
Shock Absorbers



CONNECTIONS / OTHER



HV30
Absorber intake



PHE10X10NMDE-A
Industrial shock absorbers PowerStop



KAG500
Plug-in connector Straight Cable 5m - Socket M8 (female)



KAW500
Plug-in connector Angled Cable 5m - Socket M8 (female)



ZE20H7X4
Centering Disc

Order no.	► Technical data	
	LI30-15	LI30-30
Stroke [mm]	15	30
Pressure force max. [N]	270	270
Retraction force [N]	200	200
Travel time without external load [s]	0.06	0.14
Nominal operating pressure [bar]	6	6
Operating temperature min. [°C]	5	5
Operating temperature max. [°C]	+80	+80
Air volume per cycle [cm³]	12	25
Weight [kg]	0.32	0.37
Load Fa max. [N]	70	50
Max. deflection A [mm]	0.05	0.05

- ① Fixing linear cylinder
- ② Energy supply
- ③ Fixing application
- ⑧ Fixing for adapter plate
- ⑨ Fixing for HV-flange
- ⑬ Intake proximity switch
- Ⓐ Air connection (retract)
- Ⓑ Air connection (extend)

