

MATCH - ROBOT MODULE


LWR50F-18-01-A

▶ PRODUCT SPECIFICATIONS




▶ Vertical design with centered holding force

Shows the maximum handling weight depending on acceleration and lever arm



▶ Forces and moments


Shows static forces and moments



Mr [Nm]	20
My [Nm]	40
Fa [N]	500

▶ Horizontal design with centered holding force

Shows the maximum handling weight depending on acceleration and lever arm



▶ RECOMMENDED ACCESSORIES



GRIPPING COMPONENTS



LWR50L-03-00002-A
MATCH - Grippers



LWR50L-23-00005-A
MATCH - Grippers



LWR50L-23-00006-A
MATCH - Grippers



LWR50L-23-00007-A
MATCH - Grippers



LWR50L-23-00008-A
MATCH - Grippers



CONNECTIONS / OTHER



WVM7
Angled Fittings - Quick Connect Style



ZUB123084
Strain relief

Order no.	Technical data
	LWR50F-18-01-A
Suitable for robot type	ELITE Robots
Control	Digital I/O
IO logic	NPN
Handling weight max. [kg]	25
Connecting cable	Socket, push-pull, 12-pole
Locking stroke [mm]	1
Electrical energy transfer	integrated
Pneumatic energy transfer	integrated
Tightening force [N]	50
Release force [N]	0
Repetition accuracy in X, Y [mm]	0.05
Repetition accuracy in Z [mm]	0.05
Offset at coupling max. in X,Y [mm]	1.0
Operating temperature [°C]	5 ... +60
Service life in cycles	100,000
Protection to IEC 60529	IP40
Weight [kg]	0.32

