## CLAMPING ELEMENTS | HYDRAULIC SERIES KWH

## PRODUCT ADVANTAGES




- broad range of products
   For all common profile rail guides
- Energize to close (NO) Closing with pressure
- extremely durable

Up to 10 million static clamping cycles

► THE BEST PRODUCT APPLICATION SCE- NARIOS	<ul> <li>FOR YOUR APPLICATION</li> <li>Machine table clamping of heavy cutting work centres</li> <li>Clamping of heavy handling systems</li> </ul>
FURTHER INFORMATION	<ul> <li>Spacer plate         In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).     </li> <li>Special variants on request, e.g.         With additional hydraulic connection (from above, from the front)     </li> </ul>

## **BENEFITS IN DETAIL**



- Available for all common profile rail guides

 $\fbox{1} \textbf{Profile rail guide}$ 

- 2 Return spring- Interlocked integration in the jaws
- 3 Clamping jaw
  - Pressed at the free surfaces of the profile rail guide
- (4) Housing
- 5 Membran
  - For pressurization
- 6 Scraper
  - Can also be ordered as an option

## ► INFORMATION ON THE SERIES

	Technical data
Series	КЖН
Rail size	25-65 mm
Holding force	1600-46000 N
Nominal operating pressure	100/150 [bar]
Operating pressure max.	110/160 [bar]
Spring storage	inexistent
PLUS connection	No
B10d value	up to 10 million
Dynamic braking cycles	not suitable
Operation	hydraulic
Operating temperature	-10 +70 [°C]