


CLAMPING ELEMENT | PNEUMATIC MBPS4510BS1A

► PRODUCT ADVANTAGES



► broad range of products

For all common profile rail guides

► Energize to open (NC)

through spring-loaded energy storage


► high durability

5 million static clamping cycles

► Safety element

Safe braking in case of energy failure

► TECHNICAL DETAILS



① Profile rail guide

- Available for all common profile rail guides

② Wedge-type gear

- Power transmission between the pistons and clamping jaws and brake shoes

③ Clamping jaws and brake shoes

- Pressed at the free surfaces of the profile rail guide

④ Housing

⑤ Pneumatic piston

- The piston moves the wedge-type gear longitudinally

⑥ Spring-loaded energy storage

- For non-pressurized closing of the clamping unit

► INFORMATION ON THE PRODUCTS

APPLICATION SCA- NARIOS

► Clamping in case of pressure drop

► Emergency OFF function

► Braking linear motors

FURTHER INFORMATION

► Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).


► Special variants on request, e.g.

With proximity switch monitoring

With low opening pressure (3.0 bar)

With additional air connection (from above, from the front)

► TECHNICAL DRAWINGS



(A) Connection opening (both sides possible, only one connection necessary)

(C) Quick exhaust valve (both sides)



► TECHNICAL DATA

Order no.	MBPS4510BS1A
Operation	pneumatic
Holding force [N]	3600
Theoretical holding force ($\mu=0,1$) [N]	4,500
PLUS connection possible	No
Operating pressure [bar]	4.5 ... 6.5
B10d value	5,000,000
Positioning accuracy +/- [mm]	0.05
Opening time [s]	0.23
Closing time [s]	0.035
Operating temperature [°C]	-10 ... +70
Weight [kg]	2
Function	Clamping and braking
Condition	NC (Normally Closed) closed without pressure
Installation direction	from the front
Wiper	yes
Air volume per cycle [cm ³]	44
Certifications	CE / UKCA / LABS / REACH / RoHS

Schematic drawing. General tolerances according to DIN ISO 2768 T1-f/T2-H. Edges according to ISO 13715. Element has no guiding properties. Guidance must be external. The holding force is the maximum force that can be applied in the axial direction. Each clamping and braking element is tested in a 100% inspection before delivery for the specified holding forces on a hardened steel rail with a lightly oiled lubricating layer (ISO-VG 68). The use of other lubricants or rail coatings can influence the coefficient of friction. The operating instructions must be observed before commissioning. We reserve the right to make technical changes in the course of further development. The latest and further data can be found online and in the operating instructions at www.zimmer-group.com.