CLAMPING AND BRAKING ELEMENTS | HYDRAULIC SERIES LBHS

PRODUCT ADVANTAGES



broad range of products

For all common profile rail guides

► Energize to open (NC)

through residual stress

the power pack

Up to 0.5 million static clamping cycles

Safety element

Safe braking in case of energy failure

Maximum flexibility

Additional hydraulic connection from above

► THE BEST PRODUCT FOR YOUR APPLICATION


APPLICATION SCE-**NARIOS**

- Precise positioning through maximum rigidity
- Clamping measurement applications
- Clamping and braking of heavy handling systems
- Braking in emergency OFF situations
- Clamping in case of pressure drop

FURTHER INFORMATION Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).

BENEFITS IN DETAIL



1 Profile rail guide

- Available for all common profile rail guides

2 Housing - functional component

- Generating clamping force by clamping material
- Narrow and low design

(3) Eroding contour

- Used for opening the element under pressure

4 Clamping jaws and brake shoes

- Pressed at the free surfaces of the profile rail guide

5 Sealing plates

- for double-sided hydraulic line connection

6 Scraper

- Optionally available with "A" article ending

▶ INFORMATION ON THE SERIES

	► Technical data
Series	LBHS
Rail size	20-65 mm
Operating pressure min.	120 [bar]
Operating pressure max.	130 [bar]
Spring storage	existing
PLUS connection	No
B10d value	up to 500 000
Dynamic braking cycles	up to 500
Operation	hydraulic
Operating temperature	-10 +70 [°C]