
## **CLAMPING ELEMENTS | MANUAL SERIES MINIHK**

#### PRODUCT ADVANTAGES



small construction

For all common miniature profile rail guides

- ► Tool-free opening and closing (bi-stable)
  - By turning the knurled screw
- Maintenance free

Up to 50,000 static clamping cycles

#### ► THE BEST PRODUCT FOR YOUR APPLICATION

APPLICATION SCE-**NARIOS** 

- Assembly aids
- Optical equipment
- Medical equipment


**FURTHER** INFORMATION Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).

#### **BENEFITS IN DETAIL**

- 1 Miniature profile rail guide
   Available for all common miniature profile rail guides
- (2) Stainless knurled screw
  - For opening and closing the clamping unit

- 3 Clamping jaw
  - The floating bearingsguarantee symmetrical application of force
- (4) Housing



### ► INFORMATION ON THE SERIES


TECHNICAL DATA

Rail size	5-42 mm
Holding force	40-300 N
Clamping torque knurled screw	0,07-2,5 Nm
Spring storage	inexistent
B10d value	up to 50 000
Dynamic braking cycles	not suitable
Operation	manual
Operating temperature	-10 +70 [°C]

# **CLAMPING ELEMENTS | MANUAL**

### **SERIES MINIHK**

#### PRODUCT ADVANTAGES



small construction

For all common miniature profile rail guides

- ► Tool-free opening and closing (bi-stable) By turning the knurled screw
- ▶ Maintenance free Up to 50,000 static clamping cycles

#### **BENEFITS IN DETAIL**


APPLICATION SCE-**NARIOS** 

- Assembly aids
- Optical equipment
- Medical equipment

**FURTHER** INFORMATION Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).

#### ► INFORMATION ON THE SERIES



① Miniature profile rail guide
- Available for all common miniature profile rail guides

#### 2 Stainless knurled screw

- For opening and closing the clamping unit

### 3 Clamping jaw

- The floating bearingsguarantee symmetrical application of force

4 Housing

### **▶ THE BEST PRODUCT FOR YOUR APPLICATION**

	► Technical data
Series	MiniHK
Rail size	5-42 mm
Holding force	40-300 N
Clamping torque knurled screw	0,07-2,5 Nm
Spring storage	inexistent
B10d value	up to 50 000
Dynamic braking cycles	not suitable
Operation	manual
Operating temperature	-10 +70 [°C]