

MATCH - ROBOT MODULE

LWR50F-20-04-A


PRODUCT SPECIFICATIONS



MATCH

Vertical design with centered holding force

Shows the maximum handling weight depending on acceleration and lever arm



Forces and moments


Shows static forces and moments



Mr [Nm]	20
My [Nm]	40
Fa [N]	500

Horizontal design with centered holding force

Shows the maximum handling weight depending on acceleration and lever arm



RECOMMENDED ACCESSORIES



GRIPPING COMPONENTS



LWR50L-02-00001-A
MATCH - Grippers



LWR50L-03-00001-A
MATCH - Grippers



LWR50L-22-00001-A
MATCH - Grippers



LWR50L-23-00002-A
MATCH - Grippers



CONNECTIONS / OTHER



WVM7
Angled Fittings - Quick Connect Style



ZUB123084
Strain relief

Order no.	► Technical data
	LWR50F-20-04-A
Suitable for robot type	KUKA LBR iisy Series
Control	IO-Link
Connecting flange according EN ISO 9409-1	TK 50
Handling weight max. [kg]	25
Connecting cable	Plug KukaLBR iisy
Locking stroke [mm]	1
Electrical energy transfer	integrated
Pneumatic energy transfer	integrated
Tightening force [N]	50
Release force [N]	0
Repetition accuracy in X, Y [mm]	0.05
Repetition accuracy in Z [mm]	0.05
Offset at coupling max. in X,Y [mm]	1.0
Operating temperature [°C]	5 ... +60
Service life in cycles	100,000
Protection to IEC 60529	IP40
Weight [kg]	0.29

- ① Fixing (robot side)
- ② Energy supply
- ④ pneumatic feed-through
- ⑤1 Ground
- ⑤2 Connect-LED/Freedrive (robot-specific)

