

MASTER COMMUNICATION MODULE


MCM-EC-00-00-A

▶ PRODUCT SPECIFICATIONS



- ▶ All Zimmer Group IO-Link components can be used, regardless of the structure of the existing robot / system base
- ▶ No complex cable routing through the robot or system (slip rings, contact elements etc. not required)
- ▶ No source of error due to moving data cable (mechanical obstacle, broken wire) wearing part eliminated
- ▶ Wireless range of point-to-point communication up to 10 m, up to 30 m with unobstructed view
- ▶ 8 advanced grippers, 16 basic grippers or 16 digital devices
- ▶ Industrial design
- ▶ IP67 certified
- ▶ Secure and reliable communication thanks to redundant signals and a maximum packet data error rate of 10^{-9}

▶ DEVICE CONNECTIVITY



▶ RECOMMENDED ACCESSORIES

CONNECTIONS / OTHER



CSTE01604
Straight connecting cable 2 m - M12 socket, 5-pin, L-coded



CONNECTIONS / OTHER



CSTE01605
Straight connecting cable 2 m - M12 / RJ45 plug, 4-pin, D-coded



CSTE01877
Straight connection cable 5 m - M12 socket, 5-pin, L-coded



CELE03175
TigoEngine

Order no.	Technical Data
	MCM-EC-00-00-A
Control	EtherCAT
Number of grippers, max.	16
IO-Link class	Class A/B
IO-Link version	1.1
Frequency range [GHz]	2.4
Antenna	SMA screw connector
Number of antennas [piece]	3
Supply voltage [V DC]	18 ... 32
Supported transmission protocol	COM 3
Mounting options	Screw mounting
Operating temperature [°C]	-25 ... +70
Protection to IEC 60529	IP67
Weight [g]	227

