
SPN ZERO-POINT CLAMPING SYSTEM **SPN062P2 - CLAMPING PLATE**

> 2-FOLD



- Compact design with optimized design height
- System assembly with high precision
- Integrated air supply/distribution
- ► Integrated PLUS connection
- Available with the advanced zero-point clamping system on request
- Variable mounting options

	► Technical Data	
Order no.	SPN062P2E6SD-B	SPN062P2E4SD-B
Operation mode	Pneumatic	Pneumatic
Holding force max.	2xM8	2xM8
Operating pressure [bar]	6 7	4 7
Pull-in force [kN]	2.0	1.0
Pull-in force with PLUS connection [kN]	2x5	2x2.5
Operating temperature [°C]	-10 +70	-10 +70
Rotation prevention	Yes	Yes
PLUS connection	Yes	Yes
Air cleaning	No	No
Piston position sensing	No	No
Contact monitoring	No	No
Material	Tempered stainless steel/steel	Tempered stainless steel/steel
Weight [kg]	5.4	5.4



- 1 Release
- 2 Plus connection
- 6 Mounting screw*
- 7 Thread bore transport
- (8) Sealing cap
- 9 T-slot nut*
- 10 T-slot nut mounting screw*

^{*}Not included in delivery