
# **CLAMPING ELEMENTS | PNEUMATIC**

## **SERIES MK**

#### PRODUCT ADVANTAGES



broad range of products

For all common profile rail guides

► Energize to close (NO)

Closing with pressure

high durability

Up to 5 million static clamping cycles

#### ► THE BEST PRODUCT FOR YOUR APPLICATION

APPLICATION SCE-**NARIOS** 

- Positioning of axes
- Fixing of vertical axes
- Positioning of lifting units

**FURTHER** INFORMATION Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).


Special variants on request, e.g.

With proximity switch monitoring

With additional air connection (from above, from the front)

made of stainless steel

#### **BENEFITS IN DETAIL**



- 1 Profile rail guide
  - Available for all common profile rail guides
- 2 Wedge-type gear
  - Power transmission between piston and clamping jaw
- 3 Clamping jaw
  - Pressed at the free surfaces of the profile rail guide
- 4 Housing
- 5 Pneumatic piston
  - The piston moves the wedge-type gear longitudinally

### **▶ INFORMATION ON THE SERIES**

	► Technical data
Series	MK
Rail size	12-65 mm
Holding force	350-2250 N
Pressure min. / max.	3 / 6.5
Spring storage	inexistent
PLUS connection	No
B10d value	up to 5 million
Dynamic braking cycles	not suitable
Operation	pneumatic
Operating temperature	-10 +70 [°C]