


CLAMPING ELEMENT | PNEUMATIC MKS2502KB

► PRODUCT ADVANTAGES



► broad range of products

For all common profile rail guides

► Energize to open (NC)

through spring-loaded energy storage

► high durability

5 million static clamping cycles


► Higher holding force

Via activation with PLUS air

► Safety element

Safe clamping in case of energy failure

► TECHNICAL DETAILS



① Profile rail guide

- Available for all common profile rail guides

② Wedge-type gear

- Power transmission between piston and clamping jaw

③ Clamping jaw

- Pressed at the free surfaces of the profile rail guide

④ Housing

⑤ Pneumatic piston

- The piston moves the wedge-type gear longitudinally

⑥ Spring-loaded energy storage

- For non-pressurized closing of the clamping unit

► INFORMATION ON THE PRODUCTS

APPLICATION SCENARIOS

- Clamping in case of pressure drop
- Clamping without energy requirement

FURTHER INFORMATION

► Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).

► Special variants on request, e.g.


With low opening pressure (3.0 bar)

With proximity switch monitoring

With additional air connection (from above, from the front)


made of stainless steel

► TECHNICAL DRAWINGS



(A) Connection opening (both sides possible, only one connection necessary)

(B) Vent filter (one-sided) Connection can be used as PLUS-connection (both sides possible, only one connection necessary)



► TECHNICAL DATA

Order no.	MKS2502KB
Operation	pneumatic
Holding force [N]	750
Theoretical holding force ($\mu=0,1$) [N]	938
PLUS connection possible	Yes
Holding force PLUS connection [N]	1400
Operating pressure [bar]	5.5 ... 6.5
Nominal operating pressure [bar]	6
B10d value	5,000,000
Positioning accuracy +/- [mm]	0.02
Opening time [s]	0.02
Closing time [s]	0.015
Operating temperature [°C]	-10 ... +70
Weight [kg]	0.65
Function	Clamping
Condition	NC (Normally Closed) closed without pressure
Installation direction	from above
Air volume per cycle [cm ³]	9
Clean room applications according to DIN EN ISO 14644-1	6
Certifications	CE / UKCA / LABS / REACH / RoHS

Schematic drawing. General tolerances according to DIN ISO 2768 T1-f/T2-H. Edges according to ISO 13715. Element has no guiding properties. Guidance must be external. The holding force is the maximum force that can be applied in the axial direction. Each clamping and braking element is tested in a 100% inspection before delivery for the specified holding forces on a hardened steel rail with a lightly oiled lubricating layer (ISO-VG 68). The use of other lubricants or rail coatings can influence the coefficient of friction. The operating instructions must be observed before commissioning. We reserve the right to make technical changes in the course of further development. The latest and further data can be found online and in the operating instructions at www.zimmer-group.com.