


BELLOWS SUCTION CUP

SERIES ZBF

▶ PRODUCT ADVANTAGES



▶ Diameter: 25 mm–100 mm

▶ Optimum geometry

- For thin, oily and bent metal plates and car body panels
- Profile structure on the underside of the suction cup for increased friction between the workpiece and vacuum suction cup
- Height compensation and damping function with 1.5 folds

▶ Application areas

- Automotive
- Glass
- Wood and composite materials
- Metal

▶ PRODUCT KEY


		-	PU	-	38M	-	F
Series	Diameter		Material		Fixing thread		Filter type

▶ MATERIAL CHARACTERISTICS

Version	Material	Color	Operating temperature [°C]	Shore hardness
N	NBR	Blue	-20 ... +110	60
PU	Polyurethan	Translucent orange	0 ... +60	60
S	Silicone	Red	-70 ... +200	55


▶ DIMENSIONS

ZBF25




Legend	A	B	C	D	E	F	G	H	I	J	K
Dimensions [mm]	26.5	25	25	26.6	10	23.5	17.5	26	9	26	10

ZBF30




Legend	A	B	C	D	E	F	G	H	I	J	K
Dimensions [mm]	32	27.5	27.5	29.1	10	25	18.5	30	9	27.5	10

ZBF40




Legend	A	B	C	D	E	F	G	H	I	J	K
Dimensions [mm]	42	29.1	29.1	30.7	10	27.6	17.5	31.6	9	29.1	10


ZBF50




Legend	A	B	C	D	E	F	G	H	I	J
Dimensions [mm]	51.5	37.2	39.2	38.8	10	37.2	39.7	9	37.2	11

ZBF60

Legend	A	B	C	D	E	F	G	H	I	J	K
Dimensions [mm]	62.8	41.4	43.4	43	10	43.4	43.9	9	41.4	41.4	11

ZBF80

Legend	A	B	C	D	E	F	G	H	I	J	K
Dimensions [mm]	83	49.6	52.6	52.3	10	52.6	52.1	9	49.6	50.6	11

ZBF100

Legend	A	B	C	D	E	F	G	H	I	J	K
Dimensions [mm]	102	54.3	56.3	56	10	56.3	56.8	9	54.3	54.3	11

TECHNICAL DATA

Installation size	ZBF25	ZBF30	ZBF40	ZBF50	ZBF60	ZBF80	ZBF100
Lifting force parallel at -20 kPa [kg]	0.610	0.860	1.180	2.090	6.840	9.120	11.400
Lifting force parallel at -60 kPa [kg]	1.370	3.090	6.500	9.600	12.840	17.120	21.400
Lifting force parallel -90 kPa [kg]	1.890	7.750	11.300	14.700	16.920	22.560	28.200
Lifting force vertical at -20 kPa [kg]	1.100	1.770	2.500	4.180	8.940	11.920	14.900
Lifting force vertical at -60 kPa [kg]	3.200	6.260	9.660	13.200	16.260	21.680	27.100
Lifting force vertical at -90 kPa [kg]	3.800	9.480	12.800	16.280	18.540	24.720	30.900
Volume [cm³]	2.600	6.000	7.200	11.000	22.000	59.500	103.500

Order no.	Technical data			
	Diameter [mm]	Material	Fixing thread	Filter type
ZBF25-N	25	NBR		
ZBF25-N-14F	25	NBR	G1/4" internal	
ZBF25-N-14M	25	NBR	G1/4" external	
ZBF25-N-18F	25	NBR	G1/8" internal	
ZBF25-N-M10M	25	NBR	M10 external	
ZBF25-PU	25	Polyurethan		
ZBF25-PU-14F	25	Polyurethan	G1/4" internal	
ZBF25-PU-14M	25	Polyurethan	G1/4" external	
ZBF25-PU-18F	25	Polyurethan	G1/8" internal	
ZBF25-PU-M10M	25	Polyurethan	M10 external	
ZBF25-S-14F	25	Silicone	G1/4" internal	
ZBF25-S-14M	25	Silicone	G1/4" external	
ZBF25-S-18F	25	Silicone	G1/8" internal	
ZBF25-S-M10M	25	Silicone	M10 external	
ZBF30-N	30	NBR		
ZBF30-N-14F	30	NBR	G1/4" internal	
ZBF30-N-14M	30	NBR	G1/4" external	
ZBF30-N-18F	30	NBR	G1/8" internal	
ZBF30-N-M10M	30	NBR	M10 external	
ZBF30-PU	30	Polyurethan		
ZBF30-PU-14F	30	Polyurethan	G1/4" internal	
ZBF30-PU-14M	30	Polyurethan	G1/4" external	
ZBF30-PU-18F	30	Polyurethan	G1/8" internal	
ZBF30-PU-M10M	30	Polyurethan	M10 external	
ZBF30-S-14F	30	Silicone	G1/4" internal	

BELLOWS SUCTION CUP

SERIES ZBF

Order no.	► Technical data			
	Diameter [mm]	Material	Fixing thread	Filter type
ZBF30-S-14M	30	Silicone	G1/4" external	
ZBF30-S-18F	30	Silicone	G1/8" internal	
ZBF30-S-M10M	30	Silicone	M10 external	
ZBF40-N	40	NBR		
ZBF40-N-14F	40	NBR	G1/4" internal	
ZBF40-N-14M	40	NBR	G1/4" external	
ZBF40-N-18F	40	NBR	G1/8" internal	
ZBF40-N-M10M	40	NBR	M10 external	
ZBF40-PU	40	Polyurethan		
ZBF40-PU-14F	40	Polyurethan	G1/4" internal	
ZBF40-PU-14M	40	Polyurethan	G1/4" external	
ZBF40-PU-18F	40	Polyurethan	G1/8" internal	
ZBF40-PU-M10M	40	Polyurethan	M10 external	
ZBF40-S-14F	40	Silicone	G1/4" internal	
ZBF40-S-14M	40	Silicone	G1/4" external	
ZBF40-S-18F	40	Silicone	G1/8" internal	
ZBF40-S-M10M	40	Silicone	M10 external	
ZBF50-N	50	NBR		
ZBF50-N-14F	50	NBR	G1/4" internal	
ZBF50-N-14M	50	NBR	G1/4" external	
ZBF50-N-18F	50	NBR	G1/8" internal	
ZBF50-N-38F	50	NBR	G3/8" internal	
ZBF50-N-38M	50	NBR	G3/8" external	
ZBF50-N-M10M	50	NBR	M10 external	
ZBF50-PU	50	Polyurethan		
ZBF50-PU-14F	50	Polyurethan	G1/4" internal	
ZBF50-PU-14M	50	Polyurethan	G1/4" external	
ZBF50-PU-18F	50	Polyurethan	G1/8" internal	
ZBF50-PU-38F	50	Polyurethan	G3/8" internal	
ZBF50-PU-38M	50	Polyurethan	G3/8" external	
ZBF50-PU-M10M	50	Polyurethan	M10 external	
ZBF50-S	50	Silicone		
ZBF50-S-14F	50	Silicone	G1/4" internal	
ZBF50-S-14M	50	Silicone	G1/4" external	
ZBF50-S-18F	50	Silicone	G1/8" internal	
ZBF50-S-38F	50	Silicone	G3/8" internal	
ZBF50-S-38M	50	Silicone	G3/8" external	
ZBF50-S-M10M	50	Silicone	M10 external	
ZBF60-N	60	NBR		
ZBF60-N-12F	60	NBR	G1/2" internal	
ZBF60-N-14F	60	NBR	G1/4" internal	
ZBF60-N-14M	60	NBR	G1/4" external	
ZBF60-N-18F	60	NBR	G1/8" internal	
ZBF60-N-38F	60	NBR	G3/8" internal	
ZBF60-N-38M	60	NBR	G3/8" external	
ZBF60-N-M10M	60	NBR	M10 external	
ZBF60-PU	60	Polyurethan		
ZBF60-PU-12F	60	Polyurethan	G1/2" internal	
ZBF60-PU-14F	60	Polyurethan	G1/4" internal	
ZBF60-PU-14M	60	Polyurethan	G1/4" external	
ZBF60-PU-18F	60	Polyurethan	G1/8" internal	
ZBF60-PU-38F	60	Polyurethan	G3/8" internal	
ZBF60-PU-38M	60	Polyurethan	G3/8" external	
ZBF60-PU-M10M	60	Polyurethan	M10 external	
ZBF60-S-12F	60	Silicone	G1/2" internal	
ZBF60-S-14F	60	Silicone	G1/4" internal	
ZBF60-S-14M	60	Silicone	G1/4" external	
ZBF60-S-18F	60	Silicone	G1/8" internal	
ZBF60-S-38F	60	Silicone	G3/8" internal	
ZBF60-S-38M	60	Silicone	G3/8" external	

Order no.	► Technical data			
	Diameter [mm]	Material	Fixing thread	Filter type
ZBF60-S-M10M	60	Silicone	M10 external	
ZBF80-N	80	NBR		
ZBF80-N-12F	80	NBR	G1/2" internal	
ZBF80-N-14F	80	NBR	G1/4" internal	
ZBF80-N-14M	80	NBR	G1/4" external	
ZBF80-N-18F	80	NBR	G1/8" internal	
ZBF80-N-38F	80	NBR	G3/8" internal	
ZBF80-N-38M	80	NBR	G3/8" external	
ZBF80-N-M10M	80	NBR	M10 external	
ZBF80-PU	80	Polyurethan		
ZBF80-PU-12F	80	Polyurethan	G1/2" internal	
ZBF80-PU-14F	80	Polyurethan	G1/4" internal	
ZBF80-PU-14M	80	Polyurethan	G1/4" external	
ZBF80-PU-18F	80	Polyurethan	G1/8" internal	
ZBF80-PU-38F	80	Polyurethan	G3/8" internal	
ZBF80-PU-38M	80	Polyurethan	G3/8" external	
ZBF80-PU-M10M	80	Polyurethan	M10 external	
ZBF80-S	80	Silicone		
ZBF80-S-12F	80	Silicone	G1/2" internal	
ZBF80-S-14F	80	Silicone	G1/4" internal	
ZBF80-S-14M	80	Silicone	G1/4" external	
ZBF80-S-18F	80	Silicone	G1/8" internal	
ZBF80-S-38F	80	Silicone	G3/8" internal	
ZBF80-S-38M	80	Silicone	G3/8" external	
ZBF80-S-M10M	80	Silicone	M10 external	
ZBF100-N	100	NBR		
ZBF100-N-12F	100	NBR	G1/2" internal	
ZBF100-N-14F	100	NBR	G1/4" internal	
ZBF100-N-14M	100	NBR	G1/4" external	
ZBF100-N-18F	100	NBR	G1/8" internal	
ZBF100-N-38F	100	NBR	G3/8" internal	
ZBF100-N-38M	100	NBR	G3/8" external	
ZBF100-N-M10M	100	NBR	M10 external	
ZBF100-PU	100	Polyurethan		
ZBF100-PU-12F	100	Polyurethan	G1/2" internal	
ZBF100-PU-14F	100	Polyurethan	G1/4" internal	
ZBF100-PU-14M	100	Polyurethan	G1/4" external	
ZBF100-PU-18F	100	Polyurethan	G1/8" internal	
ZBF100-PU-38F	100	Polyurethan	G3/8" internal	
ZBF100-PU-38M	100	Polyurethan	G3/8" external	
ZBF100-PU-M10M	100	Polyurethan	M10 external	
ZBF100-S	100	Silicone		
ZBF100-S-12F	100	Silicone	G1/2" internal	
ZBF100-S-14F	100	Silicone	G1/4" internal	
ZBF100-S-14M	100	Silicone	G1/4" external	
ZBF100-S-18F	100	Silicone	G1/8" internal	
ZBF100-S-38F	100	Silicone	G3/8" internal	
ZBF100-S-38M	100	Silicone	G3/8" external	
ZBF100-S-M10M	100	Silicone	M10 external	